

A-100462

Base Product



Transmission Services Cabinet (TSC), Mark 2

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type	Macro cell site enclosure
Ordering Note	For UK region only

General Specifications

Access	Front door
Batteries Supported	4
Cabinet Type	Integrated cabinet
Color	Gray Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost
Cooling	175 mm fan (1)
Door Security	Swing handle with 22mm profile cylinder
Doors, quantity	1
Mounting	Plinth Root
Rack Type	EIA 19 in
Rack Units	18

Dimensions

Height	1,422.4 mm 56 in
Width	609.6 mm 24 in
Depth	609.6 mm 24 in

Electrical Specifications

Input Power Supply	16-20A
ac Distribution Type	8-way plastic enclosure
Battery String Current, maximum	3 A-h @ 48 Vdc
dc Distribution Type	12-way dc panel Power supply unit
Generator Connection	No connection

A-100462

Power Phase	Single
Rectifier Power	800 W
Rectifiers, quantity	2
Voltage	230 Vac

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Environmental Specifications

Qualification Standards	IEC 60529: 2001 IEE Wiring Regulations BS 7671 IP55
--------------------------------	---

Packaging and Weights

Included	-48V DC Power supply unit Batteries Brackets Cooling Power Distribution
Weight, net	94.801 kg 209 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system