

FEC-36



Fiber Optic Entrance Cabinet, 36 Drawers, Wall mounted

- Provides splicing, administration and storage for outside plant (OSP) and intrafacility cables (IFC)
- Offers a cost-effective, space-saving alternative to splicing on the fiber frame
- Cabinets are designed for deployment in a building equipment area
- Bend radius protection and discrete subunit routing paths ensure easy installation
- Can deploy high count of stranded or ribbon fiber cables
- Ultra high density splice capacity dependent on splice tray used

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber entrance cabinet
Product Series	FEC

General Specifications

Access	Front
Cable Entry Location	Bottom Side Top
Cable Exit Location	Bottom Side Top
Color	Putty white
Mounting	Wall
Splice Drawers, quantity	36
Splice Trays Included, quantity	0
Splicing Capacity Note	36 times number of splices per tray (example 36x288 = 10,368)

Dimensions

Height	1,574.8 mm 62 in
Width	812.8 mm 32 in
Depth	330.2 mm 13 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Included	Grommets
-----------------	----------

FEC-36

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

