


# MT-222L

---



Adjustable Wall Mount for solid walls, 12 in stand-off

## Product Classification

**Product Type** Wall mount kit

## General Specifications

**Mounting** Solid walls

## Dimensions

**Height** 203.2 mm | 8 in

**Width** 203.2 mm | 8 in

**Length** 304.8 mm | 12 in

**Pipe Outer Diameter** 114.3 mm | 4.5 in | 60.96 mm | 2.4 in | 73.66 mm | 2.9 in | 88.9 mm | 3.5 in

**Stand-off Distance** 304.8 mm | 12 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

## Packaging and Weights

**Included** Backing plates or anchors | Wall brackets (2)

**Packaging quantity** 2

**Weight, net** 23 kg | 50.706 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

### Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

# MT-222L

---

REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code