

PFC-304L12



Powered Fiber Cable, OM3, 4 Fibers, Indoor/Outdoor, 12AWG Conductor, meter, feet

- Easy peel, stranded conductors for maximum cable flexibility and rapid access
- Polarization indentation along one side of the cable for polarity identification
- No special tools or mounting hardware required - usage of a standard "FTTH" pressure clamp for aerial installation
- Easy split of cable into three separate sections for separate routing in closures, as needed for installation
- Riser/LSZH jacket for indoor/outdoor applications

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Hybrid cable, fiber and power

Ordering Note

Minimum order quantity is 500 meter

General Specifications

Cable Type

Stranded indoor/outdoor

Fiber Short Description

PFC-L12

Jacket Color

Black

Total Fiber Count

4

Dimensions

Height Over Jacket

4.318 mm | 0.17 in

Width Over Jacket


11.43 mm | 0.45 in

Conductor Gauge

12 AWG

Outline Drawing

PFC-304L12



Electrical Specifications

Voltage Rating 300 V

Mechanical Specifications

Minimum Bend Radius, loaded 88.9 mm | 3.5 in

Minimum Bend Radius, unloaded 45.72 mm | 1.8 in

Tensile Load, long term, maximum 133.447 N | 30 lbf

Tensile Load, short term, maximum 440.374 N | 99 lbf

Vertical Rise, maximum 122.011 m | 400.3 ft

Optical Specifications

Fiber Type OM3, bend insensitive

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards Telcordia GR-20-CORE Issue 4

EN50575 CPR Cable EuroClass Fire Performance Dca

EN50575 CPR Cable EuroClass Smoke Rating s1a

PFC-304L12

EN50575 CPR Cable EuroClass Droplets Rating	d1
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Flame Test Method	IEC 60332-1-2 IEC 60754-2 IEC 61034-2 NFPA 130 UL 1666 UL 444
Jacket UV Resistance	UV stabilized

Packaging and Weights

Cable weight	109.975 kg/km 73.9 lb/kft
---------------------	-----------------------------

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- CS-5E-PFC – 50µm OM3 Bend-Insensitive Multimode Fiber