ATCB-B01-002



AISG RET Control Cable, 2 m

- Feeds data and power to RET system components
- AISG and RoHS compliant

Product Classification

Product Type AISG standard cable

General Specifications

AISG Connector A 8-pin DIN Female

AISG Connector A Body Style Straight

AISG Connector A Standard IEC 60130-9

AISG Connector B 8-pin DIN Male

AISG Connector B Body Style Straight

AISG Connector B Standard IEC 60130-9

Color Black

Data Conductor Type 0.24 mm² (24 AWG) twisted pair

EU Certification CB | CE

Power Conductor Type 0.82 mm² (18 AWG) stranded

Total Conductors, quantity 6

Dimensions

 Length
 2 m | 6.562 ft

 Diameter Over Jacket
 8 mm | 0.315 in

Electrical Specifications

Protocol AISG 1.1 | AISG 2.0

Voltage, maximum 300 V

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

COMMSCSPE®

ATCB-B01-002

Climatic Sequence Test Method IEC 60068-2-14

Cold Exposure Test Method IEC 60068-2-1

·

Damp Heat Exposure Test MethodIEC 60068-2-30, Test Condition Db

Heat Exposure Test Method IEC 60068-2-2

Ingress Protection Test Method IEC 60529:2001, IP67

Rain Simulation Test Method IEC 60068-2-18, Test Condition Ra, Method 1

UV Resistance Test Method IEC 60068-2-5, Test Condition B

Packaging and Weights

Weight, net 0.2 kg | 0.441 lb

Regulatory Compliance/Certifications

Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

