# CT-5-TUW-43-16



#### 5 dB, Tapper, 340 – 6000 MHz

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Tapper

General Specifications

**Device Type** Tapper

**Application** Indoor/Outdoor

Color White
Inner Contact Plating Silver

**Interface** 4.3-10 Female

Outer Contact Plating Trimetal

**Dimensions** 

 Height
 25 mm | 0.984 in

 Width
 43 mm | 1.693 in

 Length
 141 mm | 5.551 in

**Electrical Specifications** 

**3rd Order IMD** -165 dBc

**3rd Order IMD Test Method** Two +43 dBm carriers

Insertion Loss at Frequency Band 1.8 dB @ 340-960 MHz | 1.95dB @ 3500-4500MHz | 1.95dB @ 4900-6000MHz | 2.1

dB @ 1695-2700MHz

**Return Loss at Frequency Band** 16.5dB @ 3500-4500MHz | 17.7 dB @ 4900-6000 MHz | 17.7dB @ 340-

960MHz | 20.8 dB @ 1695-2700 MHz

Average Power, maximum 200 W

Coupling 5 dB

**Coupling Tolerance** +0.15/-0.6dB @ 698-960MHz | +0.2/-1.7dB @ 3500-4500MHz | +0.3/-0.8dB @ 4900-

6000MHz | +0/-1.3dB @ 340-380 MHz | -0.2/-1.1dB @ 380-520 MHz | ±0.6dB @

1695-2700 MHz

Page 1 of 2

# CT-5-TUW-43-16

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2700 MHz | 340 – 960 MHz | 3500 – 4500 MHz | 4900 – 6000 MHz

Peak Power, maximum 3 kW Reflected Power, maximum 200 W

Mechanical Specifications

**Coupling Nut Proof Torque** 7 N-m | 61.955 in lb

### **Environmental Specifications**

**Operating Temperature**  $-35 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-31 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

**Relative Humidity** Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP67

## Packaging and Weights

 Height, packed
 40 mm | 1.575 in

 Width, packed
 90 mm | 3.543 in

 Length, packed
 180 mm | 7.087 in

 Weight, gross
 0.3 kg | 0.661 lb

 Weight, net
 0.25 kg | 0.551 lb

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

