## E#O® Coaxial/Microduct Hybrid Buried Cable PP Coated with Tone Wire



- E#O is a solution that enables service providers the ability to bridge HFC networks to FTTx. The
  E#O composite coaxial/fiber product line combines fiber, microducts, and coaxial cable
  preinstalled in conduit
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Pre-installed in high density PE conduit for added physical protection
- One-step installation saves on construction cost
- Ideal for commercial data customers that also require video
- All products tested to industry standards

## **Product Classification**

Product Type Coaxial fiber cable-in-conduit

Product Brand E#O®

General Specifications

Conductor Elongation, maximum1 %Conductor TypeSolidInsulation Elongation, minimum200 %

**Dimensions** 

Conductor Diameter1.024 mm0.04 inInsulation Thickness, nominal0.008 mm0 in

Conductor Gauge 18 AWG

**Electrical Specifications** 

**Conductor Resistance** 87.598 ohms/km | 26.7 ohms/kft

Material Specifications

**Insulation Material Type** Polypropylene coated copper-clad steel wire

Outer Jacket Material High density polyethylene (HDPE)

Mechanical Specifications

Conductor Tensile Strength, minimum827.371 N/mm² | 120000 psiInsulation Tensile Strength, minimum31.026 N/mm² | 4500 psi

Page 1 of 2



## 8220001

## **Environmental Specifications**

Environmental Space Buried

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

