

CAABD | IP6A-12PUTP-01S-02S

Base Product



InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to dual row standard density outlet, 12 links

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Copper trunk cable assembly
Product Brand	GigaSPEED X10D® InstaPATCH® Cu

General Specifications

ANSI/TIA Category	6A
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	Information outlet
Interface Feature, connector A	Single row Standard density
Interface, Connector B	Information outlet
Interface Feature, connector B	Dual row Standard density
Link Count	12
Wiring	T568B

Dimensions

Cable Assembly Length Range (m)	5 – 90
Cable Assembly Length Range (ft)	17 – 295

Electrical Specifications

dc Resistance, maximum	0.3 ohm
Safety Voltage Rating	300 V

Ordering Tree

CAABD | IP6A-12PUTP-01S-02S

1 2 3 4 5 6 7 8 9 10 11 12												
C A A A C - 1 1 H A B B F 0 5 0												
Cable Type	Connector B			Orientation A			Orientation B					
A Cat 6A X10D – U/UTP (Plenum)	A Outlet* – Single Row Standard Density	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	1 Trident Series Flat	
B Cat 6A X10D – U/UTP (Riser)	B Outlet* – Dual Row Standard Density	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	2 Right Paired Flat	
C Cat 6A X10D – U/UTP (LSZH)	C Outlet* – Dual Row High Density	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	3 Right Series Flat	
D Cat 6A X10D – F/UTP (Plenum)	G RJ45 Plug* – Single Row Standard Density	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	4 Left Paired Flat	
E Cat 6A X10D – F/UTP (Riser)	H RJ45 Plug* – Dual Row Standard Density	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	5 Left Series Flat	
F Cat 6A X10D – F/UTP (LSZH)	J RJ45 Plug* – Dual Row High Density	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	6 Trident Paired Flat	
G Cat 6 XL – U/UTP (Plenum)	N 1100 Module	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	A Trident Series Angled	
H Cat 6 XL – U/UTP (Riser)	R 360 1100 Evolve Module	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	B Right Paired Angled	
J Cat 6 XL – U/UTP (LSZH)	S OneLink 2x6	C Right Series Angled	C Right Series Angled	C Right Series Angled	C Right Series Angled	C Right Series Angled	C Right Series Angled	C Right Series Angled	C Right Series Angled	C Right Series Angled	C Right Series Angled	
Q Cat 6A X10D – S/FTP (LSZH)	T OneLink 2x4	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	D Left Paired Angled	
R Cat 6 – U/UTP Class B Rated (LSZH)		E Left Series Angled	E Left Series Angled	E Left Series Angled	E Left Series Angled	E Left Series Angled	E Left Series Angled	E Left Series Angled	E Left Series Angled	E Left Series Angled	E Left Series Angled	
S Cat 6A – U/UTP Class B Rated (LSZH)		F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	F Trident Paired Angled	
Y Cat 6A X10D SD – U/UTP (Riser)		X Not Applicable	X Not Applicable	X Not Applicable	X Not Applicable	X Not Applicable	X Not Applicable	X Not Applicable	X Not Applicable	X Not Applicable	X Not Applicable	
Connector A	Link	Outlet Color	UOM	Length								
A Outlet* – Single Row Standard Density	B 6	0 Not Applicable	F Foot	11 XXX								
B Outlet* – Dual Row Standard Density	C 8	1 Black (BK)	M Meter	12 XXX								
C Outlet* – Dual Row High Density	D 12	2 Blue (BL)										
G RJ45 Plug* – Single Row Standard Density	E 16	3 White (WH)										
H RJ45 Plug* – Dual Row Standard Density	F 18											
J RJ45 Plug* – Dual Row High Density	G 24											
N 1100 Module												
R 360 1100 Evolve Module												
S OneLink 2x6												
T OneLink 2x4												
X Unterminated												
Bundling	Jacket Color											
H Hook-n-loop	8 White (WH)											
S Sleaving	10 Slate (SL)											
Labeling	Z Blue (BL)											
A Generic Label												

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Plenum
Flammability Rating	UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 2091B-4/23 – GigaSPEED X10D® 2091B ETL Verified Category 6A U/UTP Cable, 4 pair count
- MGS600 – GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded

2091B-4/23



GigaSPEED X10D® 2091B ETL Verified Category 6A U/UTP Cable, 4 pair count

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair cable
Product Brand	GigaSPEED X10D®


General Specifications

Product Number	2091B
ANSI/TIA Category	6A
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Note	Consult ANSI/TIA-568-C.2 Annex G for length de-rating guidance for cable installation in higher temperature environments
Pairs, quantity	4
Separator Type	Isolator
Transmission Standards	ANSI/TIA-568.2-D ISO/IEC 11801 Class EA

Dimensions

Diameter Over Jacket, nominal	7.239 mm 0.285 in
Jacket Thickness	1.295 mm 0.051 in
Conductor Gauge, singles	23 AWG

Cross Section Drawing



Electrical Specifications

dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	7.61 ohms/100 m 2.32 ohms/100 ft
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Mutual Capacitance at Frequency	6.0 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	66 %
Operating Frequency, maximum	550 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Conductor Material	Bare copper
Insulation Material	FEP
Jacket Material	PVC
Separator Material	FEP
Separator 2 Material	Polyolefin

Mechanical Specifications

2091B-4/23

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

Operating Temperature -20 °C to +75 °C (-4 °F to +167 °F)

Environmental Space Plenum

Temperature Rating, UL 105 °C | 221 °F

Flame Test Method CMP/FT6

Safety Standard UL 444

Smoke Test Method CMP/FT6 | NFPA 262

Packaging and Weights

Cable weight 60.568 kg/km | 40.7 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

MGS600

Base Product



GigaSPEED X10D® M-Series Modular Jack, RJ45, Cat6A Unshielded

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

Modular jack

Product Brand

GigaSPEED X10D®

Product Series

MGS600

General Specifications

ANSI/TIA Category

6A

Cable Type

Unshielded

Conductor Type

Solid | Stranded

Termination Type

IDC

Wiring

T568A | T568B

Dimensions

Height

19.4 mm | 0.764 in

Width

21.08 mm | 0.83 in

Depth

30.2 mm | 1.189 in

Compatible Conductor Gauge, solid

22 AWG | 24 AWG

Compatible Conductor Gauge, stranded

22 AWG | 24 AWG

Electrical Specifications

Contact Resistance Variation, maximum

20 mOhm

Contact Resistance, maximum

100 mOhm

MGS600

Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm
PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles

Material Specifications

Contact Plating Material	Precious metals
Material Type	Copper alloy High-impact, flame retardant, thermoplastic
Termination Contact Plating	Nickel

Mechanical Specifications

Plug Retention Force, minimum	133 N 29.9 lbf
Plug to Jack Mating Cycles	Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system