

1180DZ



Splice for elliptical waveguide 180

Product Classification

Product Type Elliptical waveguide connector

General Specifications

Attachment Method Tab-flare | Tool-flare

Body Style Splice

Inner Contact Plating Unplated

Interface Splice

Outer Contact Plating Unplated

Pressurizable Yes

Dimensions

Width 38.1 mm | 1.5 in

Length 74.676 mm | 2.94 in

Electrical Specifications

Insertion Loss, typical 0.01 dB

Operating Frequency Band 17.7 – 19.7 GHz

Material Specifications

Material Type Brass

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

1180DZ

Packaging and Weights

Weight, net 0.4 kg | 0.882 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss, typical 0.05√freq (GHz) (not applicable for elliptical waveguide)