

7-16 DIN Female High Power Termination Load, 70–2700 MHz

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Termination Load


General Specifications

Device Type	Termination Load
Color	Silver
Interface	7-16 DIN Female

Electrical Specifications

Return Loss, minimum	20 dB
Average Power, maximum	175 W
Impedance	50 ohm
Operating Frequency Band	70 – 2700 MHz
Peak Power, maximum	2 kW
VSWR	1.22

Derating Curve



Environmental Specifications

Operating Temperature	-33 °C to +65 °C (-27.4 °F to +149 °F)
Ingress Protection Test Method	IEC 60529:2001, IP30

Packaging and Weights

Height, packed	242 mm 9.528 in
Width, packed	165 mm 6.496 in
Length, packed	130 mm 5.118 in
Weight, gross	3.7 kg 8.157 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system