


L-DN



Fiber Optic Cable, Drop, Indoor Zero Halogen, CPR-only flame rated, Dielectric

- Fiber drop cables are typically used between the fiber terminal and the building or home and available for various indoor or outdoor applications
- Fiber drop cables are engineered to withstand the most demanding environmental conditions, including sun, heat, cold, moisture and heavy RF interference
- Superior mechanical and optical performance with unmatched stability and quality

Product Classification


Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Series	L-DN

General Specifications

Cable Type	Drop
Construction Type	Non-armored
Subunit Type	Gel-free

Ordering Tree

L-DN



Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Environmental Specifications

Installation temperature -30 °C to +60 °C (-22 °F to +140 °F)

Operating Temperature -30 °C to +60 °C (-22 °F to +140 °F)

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

Environmental Space Drop | Ducted | Façade

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable