# 5UPX0805F

10-port multibeam antenna, 10x 698–894 MHz, 5 x 13.5° HPBW, fixed electrical tilt. Ships with two T-041-GL-E mounting kits.

### General Specifications

. . . . . . . . . . . .

Antenna Type	Multibeam
Band	Single band
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Polyester fiberglass pultrusion
RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, low band	10
RF Connector Quantity, total	10
Dimensions	
Width	1574 mm   61.969 in
Depth	282 mm   11.102 in
Length	1617 mm   63.661 in
Net Weight, without mounting kit	85 kg   187.393 lb
Electrical Specifications	
Impedance	50 ohm
Operating Frequency Band	698 – 894 MHz
Polarization	±45°
Electrical Specifications	

#### **Electrical Specifications**

Frequency Band, MHz	698-894
Gain, dBi	20.6
Beamwidth, Horizontal, degrees	13
Beamwidth, Vertical, degrees	17.1

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 9, 2023

**COMMSCOPE**°

# 5UPX0805F

Beam Tilt, degrees	6
USLS (First Lobe), dB	18
Front-to-Back Ratio at 180°, dB	35
CPR at Boresight, dB	12
Isolation, Cross Polarization, dB	25
VSWR   Return loss, dB	1.43   15.0
PIM, 3rd Order, 2 x 20 W, dBc	-150
Input Power per Port, maximum, watts	300

## Electrical Specifications, BASTA

Gain by all Beam Tilts, average, dBi19.6Gain by all Beam Tilts Tolerance, dB±1.9Beamwidth, Horizontal Tolerance, degrees±2.4Beamwidth, Vertical Tolerance, degrees±3.4USLS, beampeak to 20° above beampeak, dB17Front-to-Back Total Power at 180° ± 30°, dB33CPR at Boresight, dB12	Frequency Band, MHz	698-894
Tolerance, dB±2.4Beamwidth, Horizontal Tolerance, degrees±2.4Beamwidth, Vertical Tolerance, degrees±3.4USLS, beampeak to 20° above beampeak, dB17Front-to-Back Total Power at 180° ± 30°, dB33	· · · ·	19.6
Tolerance, degreesBeamwidth, Vertical Tolerance, degrees±3.4USLS, beampeak to 20° above beampeak, dB17Front-to-Back Total Power at 180° ± 30°, dB33	•	±1.9
Tolerance, degreesUSLS, beampeak to 20° above17beampeak, dB33Front-to-Back Total Power at33180° ± 30°, dB33	'.	±2.4
beampeak, dB Front-to-Back Total Power at 33 180° ± 30°, dB	'.	±3.4
180° ± 30°, dB	•	17
CPR at Boresight, dB 12		33
	CPR at Boresight, dB	12

### Mechanical Specifications

Wind Loading @ Velocity, maximum	2,700.0 N @ 160 km/h (607.0 lbf @ 160 km/h)
Wind Speed, maximum	140 km/h (87 mph)

#### Packaging and Weights

Width, packed	1670 mm   65.748 in
Depth, packed	440 mm   17.323 in
Length, packed	1760 mm   69.291 in
Weight, gross	169 kg   372.581 lb

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 9, 2023



# 5UPX0805F

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

#### Included Products

Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

#### \* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 9, 2023

