ATC200-LITE-USB



Product Classification

Portable Controller

- Carried from site to site for RET antenna setup and optimization
- Supports up to 32 RET actuators operating in AISG 1.1 or 2.0 modes
- LED display indicates the presence of input power, output power, and data communication
- Equipped with USB and serial connectors
- Power supply efficiency is Energy Star® Level IV rated

Product Type	RET controller
General Specifications	
AISG Output Connector	8-pin DIN Female
AISG Output Connector Quantity	1
Auxiliary Interface	USB
Color	Gray Yellow
Dimensions	
Height	50.8 mm 2 in
Width	127 mm 5 in
Depth	76.2 mm 3 in
Electrical Specifications	
Input Voltage	110/240 Vac
Output Current at Voltage, continuous	3.0 A @ 24 V
Output Current at Voltage, maximum	3.0 A @ 24 V
Output Voltage, typical	24 V
Electrical Safety Standard	CB CE IEC 60950-1
Interface Protocol Signal	Data dc
Power Supply	dc Jack
Protocol	AISG 1.1 AISG 2.0
Material Specifications	

Material Type

Aluminum

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 20, 2023

COMMSCOPE°

ATC200-LITE-USB

Environmental Specifications

Operating Temperature

Relative Humidity

-40 °C to +55 °C (-40 °F to +131 °F)

Up to 95%, non-condensing

Packaging and Weights

Included

Control unit | Power supply | Site configuration worksheet | US adapter | USB cable

Weight, net

0.4 kg | 0.882 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 20, 2023

