CMAX-D-TCPUSEI53



Low PIM Directional In-building Antenna, 350-470 MHz, 617-960 MHz, 1710-2700 MHz

Product Classification

Product Type In-building antenna

General Specifications

Application Indoor

Antenna Type Directional

Antenna Array Characteristic SISO

Polarization Vertical

Color White (RAL 9016)

Mounting Poles between 30–55 mm with supplied clamps

Number of Ports 1

Pigtail Cable670-141SXE, plenum ratedRadome MaterialFiberglass, UV resistant

RF Connector Interface N Female

Dimensions

 Width
 330 mm | 12.992 in

 Depth
 90 mm | 3.543 in

 Length
 330 mm | 12.992 in

 Pigtail Length
 500 mm | 19.685 in

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1710 - 2700 MHz | 350 - 470 MHz | 617 - 806 MHz | 806 - 960 MHz

Electrical Note Values typical, unless otherwise stated

Electrical Specifications

Frequency Band, MHz 350-470 617-698 698-960 1710-2700

Page 1 of 2



CMAX-D-TCPUSEI53

Gain, dBi	5.2	7	7	9
Beamwidth, Horizontal, degrees	98	70	72	45
Beamwidth, Vertical, degrees	62	54	45	53
VSWR Return loss, dB	1.8 10.9	1.8 10.9	1.8 10.9	1.8 10.9
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153
Input Power per Port, maximum, watts	100	100	100	100

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Packaging and Weights

 Width, packed
 370 mm | 14.567 in

 Depth, packed
 170 mm | 6.693 in

 Length, packed
 470 mm | 18.504 in

Packaging quantity

Weight, gross $3 \text{ kg} \mid 6.614 \text{ lb}$ Weight, net $1.9 \text{ kg} \mid 4.189 \text{ lb}$

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant

