

Type N Male for CNT-300 braided cable

Product Classification

Product Type Braided cable connector

Product Brand CNT®

General Specifications

Body Style Straight

Inner Contact Attachment Method Captivated

Inner Contact Plating Silver

Interface N Male

Outer Contact Attachment Method Crimp

Outer Contact Plating Trimetal

Dimensions


Length 34.16 mm | 1.345 in

Diameter 20.25 mm | 0.797 in

Nominal Size 0.300 in

Outline Drawing





Electrical Specifications

Insertion Loss, typical 0.05 dB

Average Power at Frequency 360.0 W @ 900 MHz

Cable Impedance50 ohmConnector Impedance50 ohmdc Test Voltage2000 VInner Contact Resistance, maximum1 mOhm

Insulation Resistance, minimum 5000 MOhm

Operating Frequency Band 0 - 6000 MHz

Outer Contact Resistance, maximum 0.25 mOhm

Peak Power, maximum10 kWRF Operating Voltage, maximum (vrms)707 V

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0-960 MHz	1.02	40.09
1710-2200 MHz	1.036	35.05
2200-2700 MHz	1.052	31.92
2700-3000 MHz	1.058	31



3000–6000 MHz 1.135 23.98

Mechanical Specifications

Connector Retention Tensile Force 220 N | 49.458 lbf

Connector Retention Torque 0.45 N-m | 3.983 in lb

Coupling Nut Proof Torque 1.7 N-m | 15.046 in lb

Coupling Nut Proof Torque Method IEC 61169-16:9.3.6

Coupling Nut Retention Force 450 N | 101.164 lbf

Coupling Nut Retention Force Method IEC 61169-16:9.3.11

Interface Durability 500 cycles

Interface Durability Method IEC 61169-16:9.5

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-65 \,^{\circ}\text{C}$ to $+125 \,^{\circ}\text{C}$ (-85 $^{\circ}\text{F}$ to $+257 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature 20 °C | 68 °F

Average Power, Ambient Temperature 40 °C | 104 °F

Average Power, Inner Conductor Temperature 100 °C | 212 °F

Climatic Sequence Test Method IEC 60068-1

Corrosion Test Method IEC 60068-2-11

Damp Heat Steady State Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Water Jetting Test Mating Mated

Water Jetting Test Method IEC 60529:2001, IP65

Packaging and Weights

Weight, net 25.51 g | 0.056 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system





* Footnotes

Insertion Loss, typical 0.05v⁻freq (GHz) (not applicable for elliptical waveguide)

