# CMAX-OMF8-43-UWI53



### Cell-Max™ Low PIM Omni MIMO In-building Antenna, 617-6000 MHz

#### **Product Classification**

Product Type In-building antenna

Product Brand Cell-Max™

General Specifications

ApplicationIndoorAntenna TypeOmni

Antenna Array Characteristic MIMO 2x2

PolarizationLinear HorizontalColorWhite (RAL 9016)

**Mounting** Thru-hole ceiling mount (optional)

Mounting Note For antenna installation on metal ceilings, please contact your local CommScope representative

Number of Ports 2

**Pigtail Cable** 670-141SXE, plenum rated

Radome Material ASA+PC, UV stabilized

**RF Connector Interface** 4 3-10 Female

**Dimensions** 

 Height
 65 mm | 2.559 in

 Pigtail Length
 500 mm | 19.685 in

 Outer Diameter
 207 mm | 8.15 in

**Electrical Specifications** 

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2700 MHz | 3300 – 4200 MHz | 4800 – 6000 MHz | 617 – 698 MHz | 698 –

960 MHz

**Electrical Note** Values typical, unless otherwise stated

COMMSCOPE®

# CMAX-OMF8-43-UWI53

# **Electrical Specifications**

Frequency Band, MHz	617-698	698-960	1695-2700	3300-4200	4800-6000
Gain, dBi	3.8	4	4	6	6
Beamwidth, Horizontal, degrees	360	360	360	360	360
Isolation, Cross Polarization, dB	15	17	18	19	19
VSWR   Return loss, dB	1.7   11.7	1.7   11.7	1.7   11.7	1.7   11.7	1.7   11.7
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153		
Input Power per Port, maximum, watts	100	100	100	100	100

# **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

**Relative Humidity** Up to 100%

# Packaging and Weights

 Height, packed
 200 mm | 7.874 in

 Width, packed
 165 mm | 6.496 in

 Length, packed
 210 mm | 8.268 in

 Weight, gross
 0.7 kg | 1.543 lb

 Weight, net
 0.6 kg | 1.323 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



