## 4101204/10 | 2287V WTRL RG11 QD 1000



RG 11 Type Quad Shield Plenum Video Coaxial Cable, white jacket, 1000 ft = (305 m) reel

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Coaxial video cable

General Specifications

Product Number 2287V

Cable Type Series 11

Center Conductor Type Solid

Construction Type Non-armored

Jacket Color White
Supported Application Video

#### Dimensions

**Cable Length** 304.8 m | 1000 ft

Diameter Over Center Conductor, specific0.0641 in per 1 strandDiameter Over Dielectric7.061 mm | 0.278 in

**Diameter Over Inner Shield (Braid)** 7.595 mm | 0.299 in

Diameter Over Inner Shield (Tape)7.214 mm0.284 inDiameter Over Jacket, nominal9.042 mm0.356 in

**Diameter Over Jacket Tolerance** ±0.008 in

Diameter Over Outer Shield (Braid)8.204 mm0.323 inJacket Thickness0.432 mm0.017 inJacket Thickness, minimum spot0.305 mm0.012 in

Center Conductor Gauge14 AWGInner Shield (Braid) Gauge36 AWGOuter Shield (Braid) Gauge36 AWG



## 4101204/10 | 2287V WTRL RG11 QD 1000

### **Electrical Specifications**

**Capacitance** 52.493 pF/m | 16 pF/ft

Characteristic Impedance75 ohmCharacteristic Impedance Tolerance±3 ohm

Conductor dc Resistance 36.089 ohms/km | 11 ohms/kft

Dielectric Strength, conductor to shield4000 VdcJacket Spark Test Voltage2500 VacNominal Velocity of Propagation (NVP)86 %

**Shield dc Resistance** 5.577 ohms/km | 1.7 ohms/kft

**Structural Return Loss** 15 dB @ 1000-3000 MHz | 20 dB @ 5-1000 MHz

Structural Return Loss Test Method 100% Swept Tested

#### Attenuation

Frequency (MHz)	Attenuation (dB/100 ft)
1.0	0.15
10.0	0.45
50.0	0.9
100.0	1.28
200.0	1.85
400.0	2.75
700.0	3.92
900.0	4.72
1000.0	5.04
1450.0	6.67
1800.0	7.71
2200.0	8.5
3000.0	9.88

### Material Specifications

Center Conductor Material Copper-clad steel wire

**Dielectric Material** Foam FEP

Jacket Material PVC Inner Shield (Braid) Coverage  $60\ \%$ 

Inner Shield (Braid) Material Tinned copper



# 4101204/10 | 2287V WTRL RG11 QD 1000

Inner Shield (Tape) Material Aluminum/Poly

Outer Shield (Braid) Coverage 50 %

Outer Shield (Braid) Material Tinned copper

Outer Shield (Tape) Material Aluminum/Poly, non-bonded

Mechanical Specifications

Minimum Bend Radius, loaded, times20 timesMinimum Bend Radius, unloaded, times10 times

#### **Environmental Specifications**

Environmental Space Plenum

**Temperature Rating, UL** 75 °C | 167 °F

Flame Test Method CMP

Safety Standard ETL | cETL

Packaging and Weights

**Cable weight** 102.683 kg/km | 69 lb/kft

Packaging Type Reel

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





