BC-40-16



Pipe-to-Pipe Clamp, heavy duty, joins two 4 in to 9 in OD round members

Product Classification	
Product Type	Clamp set
General Specifications	
Mounting	Pipe-to-pipe
Tower Taper	Tapered
Dimensions	
Height	50.8 mm 2 in
Width	304.8 mm 12 in
Length	406.4 mm 16 in
Mounting Diameter, maximum	228.6 mm 9 in
Mounting Diameter, minimum	101.6 mm 4 in
Material Specifications	
Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Clamp halves Threaded rod
Packaging quantity	2
Weight, net	16.3 kg 35.935 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 1 of 1

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 30, 2023

