


# E14F10P79



## Ultra Compact Twin Triplexer 698-960/1350-1880/1920-2690, 4.3-10 connectors

- Ideal for small cell applications
- Compact form factor with reduced size and weight
- Suitable for space limited applications like Metro Cell, Lamp Pole, Concealment Solution and Macro Site
- New 4.3-10 connectors for improved PIM performance and size reduction
- Twin configuration
- dc/AISG pass-through on low frequency ports

## Product Classification

**Product Type** Triplexer

## General Specifications

**Color** Gray

**Modularity** 2-Twin

**Mounting** Pole | Wall

**Mounting Pipe Hardware** Band clamps (2)

**RF Connector Interface** 4.3-10 Female

## Dimensions

**Height** 88 mm | 3.465 in


**Width** 138 mm | 5.433 in

**Depth** 141.5 mm | 5.571 in

**Mounting Pipe Diameter Range** 42.6–122 mm

## Outline Drawing

# E14F10P79



## Electrical Specifications

**Impedance** 50 ohm

## Electrical Specifications, dc Power/Alarm

**dc/AISG Pass-through Path** Branch 1

**dc/AISG Pass-through, combiner** Branch 1

**dc/AISG Pass-through, demultiplexer** Branch 1

**Lightning Surge Current** 5 kA

**Lightning Surge Current Waveform** 8/20 waveform

## Electrical Specifications

**Sub-module**

1 | 2


1 | 2

1 | 2

# E14F10P79

<b>Branch</b>	1	2	3
<b>Port Designation</b>	698-960	1350-1880	1920-2690
<b>Electrical Specifications, Band Pass</b>			
<b>Frequency Range, MHz</b>	<b>698–960</b>	<b>1350–1880</b>	<b>1920–2690</b>
<b>Insertion Loss, typical, dB</b>	0.1	0.25	0.2
<b>Return Loss, typical, dB</b>	22	22	22
<b>Isolation, typical, dB</b>	52	38	38
<b>Input Power, RMS, maximum, W</b>	100	100	100
<b>Input Power, PEP, maximum, W</b>	1000	1000	1000
<b>3rd Order PIM, typical, dBc</b>	-162	-162	-162
<b>3rd Order PIM Test Method</b>	Two +43 dBm carriers	Two +43 dBm carriers	Two +43 dBm carriers

## Block Diagram



## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Corrosion Test Method</b>	IEC 60068-2-11, 30 days
<b>Environmental Test Method</b>	ETSI EN 300 019-1-4
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Volume</b>	1.7 L
<b>Weight, net</b>	3 kg   6.614 lb
<b>Weight, without mounting hardware</b>	2.5 kg   5.512 lb