
MC-HP-SERIES



MC-HP Series High Capacity Monopole Platform Kits

The MC-HP Series High Capacity Monopole Platforms feature a ring mount for monopoles ranging from 12" to 50" along with a handrail and work platform for installers plus a kicker reinforcement kit for maximum loading. Offerings include 12ft, and 14ft face widths.

- -Designed for 12" to 50" Monopoles
- Includes handrail, work platform, and kicker reinforcement kit
- Adjustable Option to enable same stand-off distance for Monopoles 15" to 50"
- Available as Base Kit or Full Kit with Antenna Pipes
- 3 Sector Solutions

Product Classification

Product Type

Monopole platform kit

General Specifications


Mounting

Monopole, 304.8-1270 mm (12-50 in) OD

Ordering Tree

Part number nomenclature

Monopole platforms





MC-HP-SERIES

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

