

DPCPWR-NODE-1000



PowerShift Metro® 1000W Remote Node, 380V to 48V converter, Small Cell Pole-Mounted

- Reduced capital/operating expenditures
- Power Input/Output Connect – Plug and Play
- LED Status Indicator- ON, Initializing, Fault and OFF
- Built in twist lock Power Input Switch

Product Classification

Product Type	Module
Product Brand	PowerShift Metro®

Dimensions

Height	328.93 mm 12.95 in
Width	242.316 mm 9.54 in
Depth	99.06 mm 3.9 in

Electrical Specifications

Input Current, nominal	4.2 A
Input Voltage Range	±190 Vdc (± 125 Vdc to ± 200 Vdc)
Input Voltage, nominal	380 Vdc
Output Current Range	0–22 A
Output Current, max	22A per port
Output Current, nominal	18.5 A
Output Power Connections, quantity	3
Output Voltage Range	-52 to -56 Vdc
Output Voltage, nominal	-54 Vdc
Electrical Safety Standard	CE IEC/EN 62368-1 UL 62368
Electromagnetic Compatibility/Interference (EMC/EMI)	GR1089 Class A
Power Efficiency	95 %
Total Output Power	1000 W

Environmental Specifications

DPCPWR-NODE-1000

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Standards Compliance

CE | EN 50581 | EN 62368-1 (LVD - Safety) | GR-1089-CORE | GR-487-CORE | UL/cUL 62368

Packaging and Weights

Packaging quantity

1

Weight, net

6.001 kg | 13.23 lb