

AT-20-43-MF



20 dB Coaxial Attenuator DC-6000 4.3-10 M-F

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Attenuator

General Specifications

Device Type Attenuator

Application Indoor

Color Silver

Inner Contact Plating Silver

Interface 4.3-10 Male

Interface 2 4.3-10 Female

Outer Contact Plating Trimetal

Electrical Specifications

Return Loss, minimum 20.8 dB

Attenuation 20 dB

Attenuation Tolerance ± 0.6 dB

Average Power, maximum 2 W

Impedance 50 ohm

Operating Frequency Band 0 – 6000 MHz

Peak Power, maximum 0.5 kW

VSWR 1.2

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Regulatory Compliance/Certifications

AT-20-43-MF

Agency

CHINA-ROHS

ROHS

UK-ROHS

Classification

Above maximum concentration value

Compliant/Exempted

Compliant/Exempted

