H-3X3-CPUSE-43-AI6



Low PIM 3x3 High Power Hybrid Matrix, 555–2700 MHz

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Hybrid matrix

General Specifications

Device Type Hybrid

Application Indoor/Outdoor

Color Silver
Inner Contact Plating Silver

Interface 4.3-10 Female

Outer Contact Plating Trimetal

Dimensions

 Height
 32 mm | 1.26 in

 Width
 162 mm | 6.378 in

 Length
 297 mm | 11.693 in

Electrical Specifications

3rd Order IMD -162 dBc

3rd Order IMD Test Method Two +43 dBm carriers

Return Loss, minimum20.8 dBAverage Power, maximum100 WCoupling5 dB

Coupling Tolerance ±1.1dB @ 698-2700 MHz | ±2.0dB @ 555-698 MHz

Impedance 50 ohm

Isolation at Frequency Band 24 dB @ 555-2700 MHz

Operating Frequency Band 555 – 2700 MHz

Peak Power, maximum 1 kW

COMMSCOPE®

H-3X3-CPUSE-43-AI6

Reflected Power, maximum 100 W VSWR 1.2

Environmental Specifications

Operating Temperature $-35 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-31 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Relative Humidity Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP65

Packaging and Weights

 Height, packed
 110 mm | 4.331 in

 Width, packed
 220 mm | 8.661 in

 Length, packed
 360 mm | 14.173 in

 Weight, gross
 2.5 kg | 5.512 lb

 Weight, net
 1.6 kg | 3.527 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted





