## BHD-12



#### Double Block Hanger for 1/2 in coaxial cable (LDF4)

## **Product Classification**

Product Type Hanger kit

Ordering Note CommScope® standard product (Global)

General Specifications

Cables per Hanger 2

**Color** Black

**Hanger Type** Double block hanger

**Mounting** Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

**Dimensions** 

Maximum Stack Height 3

 Height
 40.1 mm | 1.579 in

 Width
 33 mm | 1.299 in

 Length
 67.1 mm | 2.642 in

**Compatible Cable Diameter Range** 15.2–16.3 mm

Compatible Diameter, maximum16.3 mm | 0.642 inCompatible Diameter, minimum15.2 mm | 0.598 in

Nominal Size 1/2 in

**Electrical Specifications** 

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Engineered plastic

**Environmental Specifications** 

**COMMSCOPE®** 

# BHD-12

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**Environmental Strength Capability**Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 3.8 cm | 1.496 in

 Width, packed
 17.8 cm | 7.008 in

 Length, packed
 25.4 cm | 10 in

Packaging quantity 10

**Weight, gross** 0.37 kg | 0.816 lb

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



## \* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

