

# CML-60S-96

---



Chain Mount Base Kit, 14 in stand-off, 16 ft chain, includes pipe

## Product Classification

**Product Type** Chain mount kit

## General Specifications

**Chains, quantity** 2

**Pipe, quantity** 1

**Sectors, quantity** 1

## Dimensions

**Height** 2,438.4 mm | 96 in

**Width** 203.2 mm | 8 in

**Length** 203.2 mm | 8 in

**Chain Length** 4,902.2 mm | 193 in

**Pipe Length** 2,438.4 mm | 96 in

**Mounting Diameter, maximum** 1524 mm | 60 in

**Mounting Diameter, minimum** 203.2 mm | 8 in

**Pipe Outer Diameter** 60.96 mm | 2.4 in

**Mounting Circumference, maximum** 4,775.2 mm | 188 in

**Mounting Circumference, minimum** 635 mm | 25 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL

**Wind Rating Criteria** One 96 in x 10 in panel antenna per sector

**Wind Rating Test Method** TIA/EIA-222

# CML-60S-96

---

## Packaging and Weights

|                           |                                     |
|---------------------------|-------------------------------------|
| <b>Included</b>           | Brackets   Chains   Hardware   Pipe |
| <b>Packaging quantity</b> | 1                                   |
| <b>Weight, net</b>        | 49.3 kg   108.688 lb                |

## \* Footnotes

|                    |  |
|--------------------|--|
| <b>Wind Rating</b> | BWS—Base Wind Speed; FBC—Florida Building Code |
|--------------------|--|