

MC-FM3-24-278



Monopole Co-location 24" Stand-off Mount kit, 12 in to 50 in OD, includes 2-7 /8" OD x 96" pipe

Product Classification

Product Type Stand-off mount

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 12

Sectors, quantity 3

Dimensions

Height 2,438.4 mm | 96 in

Face Width 0 m | 0 ft

Width 279.4 mm | 11 in

Length 609.6 mm | 24 in

Pipe Length 2,438.4 mm | 96 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 304.8 mm | 12 in

Pipe Outer Diameter 73.025 mm | 2.875 in

Stand-off Distance 609.6 mm | 24 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222-G

MC-FM3-24-278

Packaging and Weights

Included	Pipe mounts Plain end pipes (3) Ring mount Stand-off arms
Packaging quantity	1
Weight, net	229.835 kg 506.7 lb