

# NG4-CABLED-MODULES

---



NG4access® Cabled Modules available in all module sizes and fiber counts up to 864 fibers

NG4 cabled modules with LC and SC connectivity enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click. Cabled modules with integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation.

Cabled modules are available in a pigtail version for splicing on frame or pre-terminated to 24-fiber microcable, conventional IFC cable or Indoor/outdoor cable.

## Cable type options:

- IFC stranded
- IFC ribbon
- Indoor/outdoor stranded
- Indoor/outdoor ribbon
- Indoor/outdoor rollable ribbon
- Microcable

## Connector type options:

- LC/UPC (front/rear)
- SC/UPC (front/rear)
- LC/APC (front/rear)
- SC/APC (front/rear)
- MPO (rear)
- stub (rear)

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cabled module
<b>Product Brand</b>	NG4access®
<b>Product Series</b>	NG4
<b>Ordering Note</b>	For fiber modules with custom cable lengths, please contact your local CommScope representative

## General Specifications

<b>Body Style</b>	Straight orientation
-------------------	----------------------

# NG4-CABLED-MODULES

---

<b>Interface, front</b>	LC/APC   LC/UPC   SC/APC   SC/UPC
<b>Interface, rear</b>	LC/APC   LC/UPC   MPO   SC/APC   SC/UPC   Stub tail

## Dimensions

<b>Height</b>	13.3 mm   0.524 in
<b>Width</b>	159.9 mm   6.295 in
<b>Depth</b>	101 mm   3.976 in

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +40 °C (+23 °F to +104 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	Up to 85%, non-condensing