


# 810010214/DB | C-016-CA-8W-M16BK/40G/GRP/E



Fiber indoor/outdoor drop cable, 16-fiber, ULSZH, loose tube, Singlemode G.652.D, gel-filled, Meters jacket marking, Black jacket color, Eca flame rating. Provides Rodent Resistance

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-CA


## General Specifications

<b>Armor Type</b>	Non-metallic rods
<b>Cable Type</b>	Loose tube
<b>Construction Type</b>	Armored
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE 810009879/DB 24 x 9 /125 OS2 ULSZH EN50575 CLASS E [Serial NUMBER] [METRE MARK]
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	16
<b>Total Fiber Count</b>	16

## Dimensions

<b>Cable Length</b>	2000 m   6,561.68 ft
<b>Buffer Tube/Subunit Diameter</b>	4 mm   0.157 in
<b>Diameter Over Jacket</b>	11 mm   0.433 in

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	320 mm   12.598 in
<b>Minimum Bend Radius, unloaded</b>	240 mm   9.449 in
<b>Tensile Load, long term, maximum</b>	750 N   168.607 lbf
<b>Tensile Load, short term, maximum</b>	3000 N   674.427 lbf
<b>Cable Crush Resistance, maximum</b>	30 N/mm   171.304 lb/in
<b>Compression</b>	30 N/mm   171.304 lb/in
<b>Compression Test Method</b>	IEC 60794-1-2 E3
<b>Impact</b>	5 N-m   44.254 in lb
<b>Impact Test Method</b>	IEC 60794-1 E4
<b>Twist</b>	5 cycles
<b>Twist Test Method</b>	IEC 60794-1 E7

## Optical Specifications

<b>Fiber Type</b>	G.652.D
-------------------	---------

## Environmental Specifications

<b>Installation temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)

# 810010214/DB | C-016-CA-8W-M16BK/40G/GRP/E

---

<b>Storage Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Eca
<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)

## Environmental Test Specifications

<b>Temperature Cycle</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-2 F1

## Packaging and Weights

<b>Cable weight</b>	108 kg/km   72.573 lb/kft
---------------------	---------------------------

## Included Products

CS-8W-250-EMEA - LightScope ZWP® Singlemode Fiber  
250um

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable