

4

3

2

1

- 1.0 GENERAL NOTES
  - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X]
  - 1.2 FOR PATENT INFO: <https://www.cs-pat.com>
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
  - 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
- 4.0 TEST
- 5.0 PACKAGING
  - 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005
  - 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
  - 5.3 EXTRA HARDWARE MAY BE SUPPLIED, BAGGED AND SHIPPED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	YX1027 14AUG24	BCROSS 40202426CMO

D

D

C


C

B

B

A

A



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;  
INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT	NOTE NO.
1	MT546120120	PIPE, 2.875"OD X 120"	1	35.44 LBS	
2	XP-2025	CROSSOVER PLATE KIT, 2-3/8 OD X 2-7/8 OD	2	8.07 LBS	

DENSITY	74.83	lbs/in <sup>3</sup>
MASS	74.83	lbs
VOLUME	263.53	in <sup>3</sup>
SURFACE AREA	3925.73	in <sup>2</sup>
HEIGHT	120"	
LENGTH	48"	
WIDTH	6.90"	

<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>			
TOLERANCES		SAP MATERIAL MASTER	
1 PLACE .X[X] ± 0.2[6.3]	3 PLACE .XXX[X] ± 0.060[1.5]	<b>SF-PK-238-278</b>	
2 PLACE .XX[X] ± 0.12[3.0]	ANGLES ± 2°		
FINISH		MATERIAL	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	NAME	DATE	TITLE
	CE YX1027	14AUG24	<b>PIPE MNT, 2-3/8" CO, 2-7/8" X 120" PIPE</b>
	RW YMENG	08/14/2024	
	AD BCROSS	08/14/2024	
	RE LMCADOWEL	08/14/2024	
ECN 40202426CMO			
SCALE	DOCUMENT NO.		
<b>1:10</b>	<b>SF-PK-238-278</b>		
SIZE	Auth Group	INSL	MODEL
<b>C</b>			
VERSION	STATUS	REVISION	VERSION
00	RE	A	00
DRAWING		REVISION	
		00	RE
		A	
			SHEET
			1 OF 1

4

3

2

1