# 760259888 | SFC-12MP-8SP-RC-GR-12-PACK



Qwik-Fuse MPO Connector, UNPINNED, Singlemode-APC, Green, for ribbon, jacketed, 12 pieces pack

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	Qwik   TeraSPEED®
Product Series	Qwik-Fuse
General Specifications	
Color	Green
Color, boot	Black
Ferrule Geometry	Factory polished
Interface	MPO/APC Female
Interface Feature	Field Installable   Fusion splice   Unpinned
Total Fiber Count	12
Dimensions	
Length	57.6 mm   2.268 in
Material Specifications	
Ferrule Material	Polymer
Mechanical Specifications	
Cable Retention Strength, maximum	11.24 lb @ 0 °
Optical Specifications	
Fiber Mode	Singlemode

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2025



# 760259888 | SFC-12MP-8SP-RC-GR-12-PACK

Fiber Type	OS2
Insertion Loss Change, mating	0.3 dB
Optical Components Standard	ANSI/TIA-568. 3-D
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.75 dB
Insertion Loss, typical	0.25 dB
Return Loss, minimum	60 dB

### **Environmental Specifications**

**Operating Temperature** 

-40 °C to +75 °C (-40 °F to +167 °F)

### Packaging and Weights

Packaging quantity

12

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



### \* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matingsInsertion Loss Change, temperatureMaximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2025

