

PS-R-V4-MS

PowerShift® V4 Main 2RU Shelf accommodates up to 6 boost modules (3 separate circuits per boost module for a total capacity of 18 RRUs) providing 48,744 watts of output power.

- Reduced capital/operating expenditures
- Engineering flexibility
- Future-ready design

PowerShift® Macro V4 Main 2RU Shelf delivers the optimal voltage to your RRUs in real-time, automatically—regardless of power supply, distance, conductor size, or RRU power requirements. It optimizes backup power delivery by solving the voltage-drop problem. Inserted between the battery and trunk cable, PowerShift automatically senses and adjusts the battery's voltage output to the power cable to compensate for the voltage drop. As the battery discharges, PowerShift continues to boost output to maintain the optimal input voltage to the RRU to increase battery backup time. PowerShift® V4 Main 2RU Shelf accommodates up to 6 boost modules (PS-2000-73) per 2RU shelf. There are 3 separate circuits per boost module for a total capacity of 18 circuits (RRU's) per 2 RU shelf. Each circuit provides a maximum output of 2,708 Watts at 73Vdc and has an integrated bypass function that automatically passes the input power through to the load connections in case of a circuit failure. After the controller (PS-CNTRL-V4) calculates the voltage drop in the power cable due to line resistance, each circuit delivers about 2,000W at 54Vdc to the RRH input.

- Reduced capital/operating expenditures
- Dynamic voltage regulation to the RRUs
- Service continuity with improved battery backup run time
- Significantly reduce installation time & wiring errors
- Future-ready design for higher-powered radios

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Shelf
Product Brand	PowerShift®
Product Series	V4
Warranty	For more information, please consult our Product Warranty guidelines

General Specifications

Application	Mounts PowerShift® modules
Color	Silver metallic
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed

PS-R-V4-MS

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	609.6 mm 24 in

Electrical Specifications

Input Voltage Range	-38 to -58 Vdc
Input Voltage, nominal	-54 Vdc
Output Power Connections, quantity	18
Output Voltage Range	-48 to -73 Vdc
Output Voltage, nominal	-54 Vdc
Electrical Safety Standard	CAN/UL62368-1 CE UL60950-UL/cUL with CB report
Power Efficiency	97 %

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Relative Humidity	Up to 95%, non-condensing
Standards Compliance	EN 55022 (Emissions) RoHS Compliant Telcordia™ GR-1089 Lightning /Surge UL/cUL 62368

Packaging and Weights

Packaging quantity	1
Weight, net	11.521 kg 25.4 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

PS-R-V4-MS

Warranty

For more information, please consult our Product Warranty guidelines