



MFPS Fiber Optic panel, 1RU, 4 splitters 1x16, right side orientation, LC /APC grade B

- Compatible with most common cable types: loose tube, central core, slotted core
- Suitable for cabinets and POP locations
- Various available panel heights to support termination counts from 12 to 288
- Simple wrap-around design for easy fiber routing
- Supports patch cord diameters of 1.2 to 2.4mm (XD-series require the usage of 1.2mm patch cords)

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter patch panel
Product Series	MFPS

General Specifications

Functionality	Splitting
Color	Gray
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	LC/APC
Patch Cord Entry Location	Front, right side
Patch Cord Routing	Right sided
Rack Type	EIA 19 in ETSI 600 mm
Rack Units	1
Shelf Movement	Hinged
Split Ratio	Symmetrical
Splitter Type	1 x 16
Splitter, quantity	4
Total Ports, quantity	64
Transmission Standards	ETSI EN 300 019-1-3 IEC 61300-3-34

Dimensions

760259685 | MFPS-KED-P-YRLG-04116P

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	279.91 mm 11.02 in

Material Specifications

Finish	Powder coated
Material Type	Ethylene-propylene (EP) Polyethylene terephthalate (PET)

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A1
Directivity, minimum	55 dB
Performance Grade	Superior B grade
Polarization Dependent Loss, maximum	0.3 dB
Uniformity, maximum	1.5 dB
Insertion Loss, Splitter, maximum	14.1 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +176 °F)
Flammability Rating	UL 94 V-0

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

* Footnotes

Performance Grade	Guarantee to meet IEC 61755-1 Random Mating requirement
--------------------------	---