

FEATURES

- Ultra-High Bandwidth:
 - Higher Speed PON Ready (50G-PON)
 - Up to 400 Gbps/Slot backplane
 - N x 100GE Uplink Interfaces
 - GPON, NG-PON2, XGS-PON
 - Active Ethernet (ptp) 10G/1G
- High Availability:
 - Commons redundancy (Power/Switch Fabric/Uplinks)
 - ESRP, LAG/LACP Uplink Protection
 - Type B protection for the ODN domain
- Virtualization and Slicing:
 - Supports seamless migration toward a fully virtualized network environment
 - Several virtual network operators can share infrastructure

The PON Evo™ 12800 Series OLT is a next-generation OLT system. Part of CommScope's central office connectivity portfolio, the 128000 Series provides ultra-high bandwidth services across high-density geographic areas, supporting Metro and Urban environments to comprehensively address the entire access network. It serves both B2C and B2B markets, meeting the needs of Residential, Business, and Mobile customer segments.

The PON Evo 12800 Series OLT complies with all the relevant ITU technology standards, such as GPON (ITU-T G.984.x) and XGS-PON (ITU-T G.9807.1), using Multi-PON-Module (MPM) optical interfaces. NG-PON2 (ITU-T G.989.x) and next-generation 50G PON (ITU-T G.hsp) technologies are supported by the chassis, thus ensuring future-proof investments. The solution also provides active Ethernet Point-to-Point (P2P) connectivity with 1GE and 10GE data rates over a single fiber, covering dedicated P2P network scenarios.


Each PON port may serve up to 128 Optical Network Terminals (ONTs), assuming a maximum splitting ratio of 1:128.



CommScope PON Evo 12800 Series OLT

Architecture

The PON Evo 12800 Series OLT is carrier-grade equipment with high availability performance levels and reliability achieved through common element protection, featuring redundant Power Feed, Switching Fabric, processing and cooling components. Type B protection is available for the subscriber side, while for the network side, star and ring topologies are available with multiple 10GE and/or 100GE optical interfaces supported by the Link Aggregation Control Protocol (LAG/LACP) and the Ethernet Ring Protection Switching (ERPS ITU-T G.8032) protocol. The PON Evo 12800 Series OLT system is designed to support extended temperature ranges, making it suitable to be deployed in Outside Plant (OSP) Cabinets.



SPECIFICATIONS

| Characteristics | Specification |
|---|---|
| Physical | |
| Dimensions, H x W x D | 7RU x 48.5 cm x 24.0 cm (7RU x 19.10 in x 9.45 in) |
| Line Technology | |
| | Advanced Encryption Standard (AES); Forward Error Correction (FEC) Up to 128 ONT/Us per PON; T-CONTs: 1024 per PON; Logical Range: 60 km Maximum Differential Distance: 40 km GPON (ITU-T G.984) D/U: 2.5/1.25 Gbps XG-PON (ITU-T G.987) D/U: 10/2.5 Gbps XGS-PON (ITU-T G.9807.1) D/U: 10/10 Gbps NG-PON 2 (ITU-T G.989) D/U: 4 x 10/10Gbps P2P 1GE (ITU-T G.986) D/U: 1/1 Gbps P2P 10GE (ITU-T G.986) D/U: 10/10 Gbps |
| Capacity Specifications | |
| | 2x Switch Fabric/processing/uplink modules (Active/Active) 8x Line card slots 2x Power IN, 1 x Cooling module (3 + 3 Fans) |
| Switch Fabric Specifications | |
| | 2x Cx12800-SFU-1.6T-400 (Full Duplex, Non-Blocking); Uplink: Up to 4x10/100GbE(SFP+/SFP-DD) + 1x100/400GbE (QSFP-DD) DWDM Uplink supported |
| Line Cards | |
| | UC-G16 (16x GPON), UC-GX16 (16x GPON/XG(S)-PON), AC-E48-10G (48GbE or 16GbE + 16 10GE) |
| Layer 2 Services | |
| Services | 1:1, N:1 (TR-156i3); VLAN-ID conversion to GEM port-ID; Transparent Add/change S-TAG and C-TAG; Priority bits (p-bits) included in changes |
| Performance | GPON full wire speed. VLAN Business Ethernet Services/Transparent VLAN Services (VBES/TLS). |
| IPTV Features | |
| | IGMPv2/v3 snooping with proxy reporting; IPTV streams forwarding: 1024 |
| Timing/Synchronization | |
| | SYNC-E, IEEE1588v2/PTP, GNSS (Global Navigation Satellite System) |
| Protection | |
| | Load balancing and LACP (IEEE 802.3ad) capabilities on uplink interfaces, Type B protection on xPON interfaces, Ethernet Ring Protection Switching (ERPS ITU-T G.8032), Common element protection (processing, switch fabric, power and Fan modules). |
| Management and Security | |
| | Local management by Command Line Interface (CLI) Remote management using SNMP and HTTP protocols Centralized management using CommScope PON Evo™ SDN Management and Control CPE remote management over OMCI G.988 channel with ONU software upgrade capability Anti-MAC and IP spoofing with DAI and IPSG Access Control Lists & MAC limiting; Storm control of unicast, multicast and broadcast traffic In-band and Out-of-band Management: CLI, SNMP, XML RADIUS/TACACS+ login authentication End-to-end Zero-Touch Provisioning (ZTP) capabilities |
| Environment | |
| Operating Temperature Range | -40° to +65°C (-40° to 149°F) |
| Humidity | 5%–95% of Relative |
| Powering | |
| Power Supply | -48 V DC Input Voltage, Voltage Range -40.5 V DC to 57 V DC |
| Power Consumption (Watts @ -48 V, 25°C) | < 7.2 W (assuming full chassis), Maximum power consumption per PON port |
| Compliance | |
| Power | ETSI EN300 132-2 V2.1.1 (2003-01) Recommendation |
| Earth Protection | ETSI ETS 300 253 Jan 1995 Recommendation |
| EMC | ETSI 300 386 |
| Environmental | EN 300 019-2-1 (Storage, Class 1,2) EN 300 019 2-2 (Transportation, Class 2,3) Equivalent to ATIS-0600010.01.2008 Class 2, Harsh–Protected Environment GR-3108 Class 2 ETSI 300 019-1-3 - Class 3.3 |
| LED Indicators | |
| | Fan-Module Status; ON; PRC; LCK; HLR 1/10/25GE, 40G/100GE Power: P1, P2 |

ORDERING INFORMATION

| Model Name | Part Number | Description |
|---|-----------------------|---|
| Optical Line Terminal | | |
| PON Evo 12800 Series OLT | OLT-128-7RU | Modular Shelf OLT 7RU/19" 8 Slots 6.4Tb/s 128xPON Ports |
| | OLT-128-PWR-U | 12800 Series OLT Power Entry Module |
| | OLT-128-SFU-1.6-4 | 12800 Series OLT 1.6Tb Switch Fabric 4x100GE Uplink |
| | OLT-128-DC-KIT | 12800 Series OLT DC Power Kit w/Breaker |
| Optical Line Terminal (Line Cards) | | |
| PON Evo 12800 Series OLT | OLT-G16-GPON | Modular OLT Series 16x GPON Port Line Card |
| | OLT-GX16-MPM | Modular OLT Series 16x MPM Port Line Card |
| | OLT-AC-E48-10G | Modular OLT Series 48x 10G AE Port Line Card |
| SFP/SFP+ Optics | | |
| User Network Interface PON SFP GPON | SFP-GPON-BPLUS-CT | SFP OLT GPON Class B+ Commercial Temp |
| | SFP-GPON-BPLUS-IT | SFP OLT GPON Class B+ Industrial Temp |
| | SFP-GPON-CPLUS-CT | SFP OLT GPON Class C+ Commercial Temp |
| | SFP-GPON-CPLUS-IT | SFP OLT GPON OLT C+ Class Industrial Temp (IT) |
| | SFP-GPON-D-CT | SFP GPON OLT D Class Commercial Temp (CT) |
| | SFP-GPON-D-IT | SFP GPON OLT D Class Industrial Temp (IT) |
| User Network Interface PON SFP+ MPM | SFP-MPM-CPLUS-CT | SFP+ MPM (XGS-PON/GPON) C+ Class Commercial temp (CT) |
| | SFP-MPM-CPLUS-IT | SFP+ MPM (XGS-PON/GPON) C+ Class Industrial Temp (IT) |
| | SFP-MPM-CPLUS-ET | SFP+ MPM (XGS-PON/GPON) C+ Class Extended Temp (ET) |
| | SFP-MPM-D-ET | SFP+ MPM (XGS-PON/GPON) D Class Extended Temp (ET) |
| User Network Interface PON SFP Dual Density | SFP-DD-G-CPLUS-IT | PON OLT GPON DD SFP+ C+ Class Industrial Temp (IT) |
| | SFP-DD-XG-N2-ET | PON OLT XGS DD SFP+ N2 Class Extended Temp (ET) |
| Virtual Broadband Gateway (vBNG) | | |
| vBNG Evo Control Plane | AXC-BNG-BASE-SW | vBNG Evo Control Plane Base License |
| | AXC-BNG-1K-S | Control Plane 1K BNG Subscriber sessions |
| | AXC-BNG-10K-S | Control Plane 10K BNG Subscriber sessions |
| | AXC-BNG-100K-S | Control Plane 100K BNG Subscriber sessions |
| | AXC-BNG-500K-S | Control Plane 500K BNG Subscriber sessions |
| vBNG Evo User Plane | AXC-BNG-UP-BASE | vBNG User Plane Base License |
| | AXC-BNG-10G-BW | User Plane Bandwidth 10G |
| | AXC-BNG-40G-BW | User Plane Bandwidth 40G |
| vBNG Evo vBNG Bundles | AXC-BNG-10G-20K-PKG | Bundle 20K Control Plane Subscriber Sessions and 10G User Plane Bandwidth |
| | AXC-BNG-20G-20K-PKG | Bundle 20K Control Plane Subscriber Sessions and 20G User Plane Bandwidth |
| | AXC-BNG-100G-20K-PKG | Bundle 20K Control Plane Subscriber Sessions and 100G User Plane Bandwidth |
| | AXC-BNG-100G-64K-PKG | Bundle 64K Control Plane Subscriber Sessions and 100G User Plane Bandwidth |
| | AXC-BNG-200G-128K-PKG | Bundle 128K Control Plane Subscriber Sessions and 200G User Plane Bandwidth |
| | AXC-BNG-400G-256K-PKG | Bundle 256K Control Plane Subscriber Sessions and 400G User Plane Bandwidth |
| vBNG Evo Enhanced Services | AXC-BNG-CGN-10G-BW | Enhanced Carrier Grade NAT Bandwidth 10G |
| | AXC-BNG-CGN-100G-BW | Enhanced Carrier Grade NAT Bandwidth 100G |
| | AXC-BNG-SGRE-BASE | Enhanced Soft GRE License |

Contact Customer Care for product information and sales:

- United States: 888-944-4357
- International: +1-215-323-2345



Note: Specifications are subject to change without notice.

Copyright Statement: © 2025 CommScope, LLC. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners.

7863693_12800 Series_OLT_DS_RevA