

# P-004-DS-5M-FSU

---

Fiber indoor cable, LazrSPEED® Plenum Distribution Cable, 4 fiber single-unit, Multimode OM2+, Feet jacket marking

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   Latin America   Middle East/Africa   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber indoor cable  |
| <b>Product Series</b>        | P-DS  |


## General Specifications

|                             |              |
|-----------------------------|--------------|
| <b>Cable Type</b>           | Distribution |
| <b>Construction Type</b>    | Non-armored  |
| <b>Fiber Type, quantity</b> | 4            |
| <b>Jacket Marking</b>       | Feet         |
| <b>Subunit Type</b>         | Gel-free     |
| <b>Total Fiber Count</b>    | 4            |

## Dimensions

|                             |                    |
|-----------------------------|--------------------|
| <b>Diameter Over Jacket</b> | 4.25 mm   0.167 in |
|-----------------------------|--------------------|

## Representative Image



# P-004-DS-5M-FSU

---

## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 64 mm   2.52 in                       |
| <b>Minimum Bend Radius, unloaded</b>     | 43 mm   1.693 in                      |
| <b>Tensile Load, long term, maximum</b>  | 200 N   44.962 lbf                    |
| <b>Tensile Load, short term, maximum</b> | 667 N   149.948 lbf                   |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 100 cycles                            |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 5.88 N-m   52.042 in lb               |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 500 m   1,640.42 ft                   |

## Optical Specifications

|                   |   |
|-------------------|---|
| <b>Fiber Type</b> | OM2+, LazrSPEED® 150   OM2+, LazrSPEED® 150 |
|-------------------|---|

## Environmental Specifications

|                                      |                                       |
|--------------------------------------|---------------------------------------|
| <b>Installation temperature</b>      | 0 °C to +70 °C (+32 °F to +158 °F)    |
| <b>Operating Temperature</b>         | -20 °C to +70 °C (-4 °F to +158 °F)   |
| <b>Storage Temperature</b>           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-83-596   Telcordia GR-409 |
| <b>Environmental Space</b>           | Plenum                                |
| <b>Flame Test Listing</b>            | NEC OFNP (ETL) and c(ETL)             |
| <b>Flame Test Method</b>             | NFPA 262                              |

## Environmental Test Specifications

|                             |                                     |
|-----------------------------|-------------------------------------|
| <b>Heat Age</b>             | -20 °C to +85 °C (-4 °F to +185 °F) |
| <b>Heat Age Test Method</b> | IEC 60794-1 F9                      |
| <b>Low High Bend</b>        | -20 °C to +70 °C (-4 °F to +158 °F) |

# P-004-DS-5M-FSU

---

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11           |
| <b>Temperature Cycle</b>             | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1             |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 18 kg/km   12.095 lb/kft |
|---------------------|--------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



## Included Products

|          |  |
|----------|--|
| CS-5M-TB | – LazrSPEED® 150 OM2+ Bend-Insensitive Multimode Fiber |
|----------|--|

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable