

# 760210922 | HRC-24SM-1206C-1818-APV

---

HELIAX® Hybrid Cable with Concentric Conductors, UL Type RHC

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable, copper and fiber
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Application</b>	Remote radio head
<b>Alarm Wire, quantity</b>	18
<b>Cable Type</b>	Wireless feeder
<b>Conductors, quantity</b>	12
<b>Construction Type</b>	Shielded
<b>Fiber Short Description</b>	RFF-6 AWG concentric
<b>Inner Shield (Tape) Material</b>	Corrugated aluminum
<b>Jacket Color</b>	Black
<b>Outer Shield (Tape) Material</b>	PVC
<b>Strength Members</b>	Glass reinforced plastic rod
<b>Subunit, quantity</b>	2
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	24
<b>Water Blocking Method</b>	Water blocking tape(s)   Water blocking threads

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	9.144 mm   0.36 in
<b>Diameter Over Jacket</b>	43.434 mm   1.71 in
<b>Alarm Wire Gauge</b>	18 AWG
<b>Conductor Gauge</b>	6 AWG concentric


## Electrical Specifications

<b>dc Resistance Note</b>	Maximum value based on a standard condition of 20 °C (68 °F)
---------------------------	--

**dc Resistance, maximum**

1.352 ohms/km | 0.412 ohms/kft

## Representative Image



## Material Specifications

**Ripcord Material** Para-aramid synthetic fiber

## Mechanical Specifications

<b>Minimum Bend Radius, multiple bends, loaded</b>	868.68 mm   34.2 in
<b>Minimum Bend Radius, multiple bends, unloaded</b>	520.7 mm   20.5 in
<b>Minimum Bend Radius, single bend, unloaded</b>	119.38 mm   4.7 in
<b>Tensile Load, long term, maximum</b>	2,001.699 N   450 lbf
<b>Tensile Load, short term, maximum</b>	6,672.33 N   1500 lbf
<b>Compression</b>	4.465 kg/mm   250 lb/in
<b>Compression Test Method</b>	FOTP-41
<b>Flex Test Method</b>	FOTP-104
<b>Impact</b>	4.34 ft lb   5.884 N-m
<b>Impact Test Method</b>	FOTP-25
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	FOTP-85

## Optical Specifications

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

## Environmental Specifications

<b>Installation temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Storage Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-104-696   ANSI/ICEA S-87-640   Telcordia GR-20   Telcordia GR-409   UL 2882
<b>Environmental Space</b>	Wireless installation

## Packaging and Weights

<b>Cable weight</b>	2,854.298 kg/km   1918 lb/kft
---------------------	-------------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

CS-8G-MP	-	Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)
----------	---	--

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable