

R-072-DZ-6F-FMU

Fiber indoor cable, OptiSPEED® Riser Distribution, interlocking aluminum armored with riser jacket, 72 fiber multi-unit with 12 fiber subunits, Multimode OM1, Feet jacket marking

Product Classification

Regional Availability	Asia Australia/New Zealand Latin America Middle East /Africa North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	R-DZ

General Specifications

Armor Type	Interlocking aluminum
Cable Type	Distribution
Construction Type	Armored
Fiber Type, quantity	72
Fibers per Subunit, quantity	12
Jacket Marking	Feet
Subunit Type	Gel-free
Subunit, quantity	6
Total Fiber Count	72

Dimensions

Buffer Tube/Subunit Diameter	5.95 mm 0.234 in
Diameter Over Armor	26.04 mm 1.025 in
Diameter Over Jacket	28.1 mm 1.106 in

Representative Image

R-072-DZ-6F-FMU



Mechanical Specifications

Minimum Bend Radius, loaded	561 mm 22.087 in
Minimum Bend Radius, unloaded	393 mm 15.472 in
Tensile Load, long term, maximum	400 N 89.924 lbf
Tensile Load, short term, maximum	1335 N 300.12 lbf
Compression	85 N/mm 485.363 lb/in
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	35 N-m 309.776 in lb
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7
Vertical Rise, maximum	69 m 226.378 ft

Optical Specifications

Fiber Type	OM1, OptiSPEED® OM1, OptiSPEED®
-------------------	-----------------------------------

Environmental Specifications

R-072-DZ-6F-FMU

Installation temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596 Telcordia GR-409
Environmental Space	Riser
Flame Test Listing	NEC OFCR (ETL) and c(ETL)
Flame Test Method	UL 1666

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Packaging and Weights

Cable weight	591 kg/km 397.134 lb/kft
---------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-6F-TB – OptiSPEED® OM1 Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable