


CPC5392-09 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM



GigaSPEED® XL VisiPatch® to GigaSPEED® XL GS8E Low Smoke Zero Halogen Cordage 4 Pair Hybrid Patch Cord, Yellow Jacket

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Twisted pair patch cord
Product Brand	GigaSPEED XL® VisiPatch®
Product Series	CPC

General Specifications

ANSI/TIA Category	6
Cable Type	U/UTP (unshielded)
Conductor Type	Stranded
Interface, Connector A	VisiPatch®
Interface Feature, connector A	Standard
Interface, Connector B	RJ45 plug
Interface Feature, connector B	Standard
Jacket Color	Yellow
Pairs, quantity	4
Wiring	T568B

Dimensions

Cable Assembly Length, minimum (ft)	1
Cable Assembly Length, maximum (ft)	100
Cable Assembly Length, minimum (m)	1
Cable Assembly Length, maximum (m)	30

CPC5392-09 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	White/Orange
Position 2	Blue	Orange
Position 3	White/Orange	Lt. Green
Position 4	Orange	Blue
Position 5	Lt. Green	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Electrical Specifications

dc Resistance, maximum 0.3 ohm

Ordering Tree

CPC -

Outlet Color

0	Not applicable
1	Black
2	Blue
3	Gray
4	Green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac

Jacket Color

1	Black
2	Light blue
3	Dark gray
4	Spring green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac
C	Gray
K	Pink
L	Violet
M	Green
Z	Blue

UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

Length

12

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

Contact Plating Material Precious metals

Material Type Copper alloy | Polycarbonate

CPC5392-09 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

Mechanical Specifications

Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N 9.892 lbf

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Safety Standard	ETL cETL

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

860498633 3074E YEL C6 4/24 SR U/UTP RVAR	–	GigaSPEED XL® 3074E Category 6 U/UTP Cable, low smoke zero halogen, yellow jacket, 4 pair count, variable length, reel
---	---	--