

F4S-DMDF-M5-P

RSJ4-50 SureFlex® Jumper with interface types 7/16 DIN Male and 7-16 DIN Female, 0.55 m



Product Classification

| | |
|-----------------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|-----------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Straight |
| Interface, Connector A | 7-16 DIN Male |
| Interface, Connector B | 7-16 DIN Female |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|-----------------|
| Length | 0.5 m 1.64 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static | -116 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz | 1.065 | 30.04 |
| 1700–2200 MHz | 1.065 | 30.04 |
| 2200–2700 MHz | 1.106 | 25.96 |

Jumper Assembly Sample Label

F4S-DMDF-M5-P



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |