

# CPC5482-08 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

---

GigaSPEED XL® VisiPatch® Single-ended 4-pair Solid Patch Cord, White Jacket

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Twisted pair patch cord
<b>Product Brand</b>	GigaSPEED XL®   VisiPatch®
<b>Product Series</b>	CPC

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type</b>	Solid
<b>Interface, Connector A</b>	VisiPatch®
<b>Interface Feature, connector A</b>	Standard
<b>Interface, Connector B</b>	Unterminated
<b>Interface Feature, connector B</b>	Standard
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4
<b>Wiring</b>	VisiPatch®

## Dimensions

<b>Cable Assembly Length, minimum (ft)</b>	1
<b>Cable Assembly Length, maximum (ft)</b>	100
<b>Cable Assembly Length, minimum (m)</b>	1
<b>Cable Assembly Length, maximum (m)</b>	30

## Wiring Diagram

# CPC5482-08 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

	Connector A	Connector B
Position 1	Lt. Blue	
Position 2	Blue	
Position 3	White/Orange	
Position 4	Orange	
Position 5	Lt. Green	
Position 6	Green	
Position 7	Lt. Brown	
Position 8	Brown	

## Electrical Specifications

**dc Resistance, maximum** 0.3 ohm

## Ordering Tree

CPC     - <sup>9</sup> <sup>10</sup> <sup>11</sup> <sup>12</sup>

### Outlet Color

0	Not applicable
1	Black
2	Blue
3	Gray
4	Green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac

### Jacket Color

1	Black
2	Light blue
3	Dark gray
4	Spring green
5	Ivory
6	Orange
7	Red
8	White
9	Yellow
B	Lilac
C	Gray
K	Pink
L	Violet
M	Green
Z	Blue

### UOM

11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

### Length

12

### Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Material Specifications

**Contact Plating Material** Precious metals

**Material Type** Copper alloy | Polycarbonate

## Mechanical Specifications

# CPC5482-08 | DO NOT USE - THIS PRODUCT NOW EXISTS AS AN ITEM

---

<b>Plug Insertion Life, minimum</b>	200 times
<b>Plug Retention Force, minimum</b>	44 N   9.892 lbf

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Environmental Space</b>	Non-plenum
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	ETL   cETL

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

860062660 1071E WHT C6 4/23 U/UTP RVAR	-	GigaSPEED XL® 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, white jacket, 4 pair count, variable length, reel
--	---	--