

CCVVPX308.11R-C3

8-port sector antenna, 4x 790–960 and 4x 1695–2690 MHz, 65° HPBW, 4x RET with manual override. Bands cascaded SRET.



- Integrated Internal Remote Electrical Tilt (RET), with independent control of electrical tilt with manual override on all arrays
- All Internal RET actuators are connected in “Cascaded SRET” configuration
- The RET interface comprises one pair of AISG input/output ports
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector

OBSOLETE

This product was discontinued on: **March 31, 2023**

Replaced By:

RRVV-65B-R4-V2

8-port sector antenna, 4x 694–960 and 4x 1695–2690 MHz, 65° HPBW, 4x RET

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-EN
Radome Material	Fiberglass, UV resistant
Radiator Material	Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, high band	4
RF Connector Quantity, low band	4
RF Connector Quantity, total	8

Remote Electrical Tilt (RET) Information

RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male

CCVVPX308.11R-C3

Input Voltage	10–30 Vdc
Internal RET	High band (2) Low band (2)
Power Consumption, idle state, maximum	2 W
Power Consumption, normal conditions, maximum	13 W
Protocol	3GPP/AISG 2.0 (Single RET)

Dimensions

Width	498 mm 19.606 in
Depth	197 mm 7.756 in
Length	2100 mm 82.677 in
Net Weight, without mounting kit	39 kg 85.98 lb

Array Layout




Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	790-960	1-2	1	ARxxxxxxxxxxxxxxxx1
R2	790-960	3-4	2	ARxxxxxxxxxxxxxxxxX2
Y1	1695-2690	5-6	3	ARxxxxxxxxxxxxxxxx3
Y2	1695-2690	7-8	4	ARxxxxxxxxxxxxxxxx4

Left Right
Bottom

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration

CCVVPX308.11R-C3



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 790 – 960 MHz
Polarization	±45°

Electrical Specifications

Frequency Band, MHz	790–862	880–960	1695–1880	1850–1990	1920–2180	2300–2500	2500–2690
Gain, dBi	14.9	15.6	16.6	16.8	17.4	18.1	18.2
Beamwidth, Horizontal, degrees	74	63	63	66	68	62	63
Beamwidth, Vertical, degrees	11.3	10.2	7.6	7	6.6	5.6	5.2
Beam Tilt, degrees	0–10	0–10	0–10	0–10	0–10	0–10	0–10
USLS (First Lobe), dB	18	18	18	18	18	18	18
Front-to-Back Ratio at 180°, dB	35	35	34	38	40	39	40
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28
Isolation, Inter-band, dB	28	28	28	28	28	28	28
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150

CCVVPX308.11R-C3

Input Power per Port, maximum, watts	300	300	250	250	250	250	250
---	-----	-----	-----	-----	-----	-----	-----

Electrical Specifications, BASTA

Frequency Band, MHz	790–862	880–960	1695–1880	1850–1990	1920–2180	2300–2500	2500–2690
Gain by all Beam Tilts, average, dBi	14.7	15.4	16.4	16.5	16.9	17.8	17.9
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.3	±0.4	±0.6	±0.7	±0.5	±0.5
Gain by Beam Tilt, average, dBi	0° 14.7 5° 14.7 10° 14.6	0° 15.5 5° 15.5 10° 15.4	0° 16.4 5° 16.4 10° 16.4	0° 16.5 5° 16.5 10° 16.4	0° 16.9 5° 16.9 10° 16.9	0° 17.9 5° 17.9 10° 17.7	0° 17.8 5° 17.9 10° 17.9
Beamwidth, Horizontal Tolerance, degrees	±4.2	±4.7	±3.3	±7.3	±4.4	±3.4	±2.6
Beamwidth, Vertical Tolerance, degrees	±0.5	±0.4	±0.5	±0.3	±0.5	±0.2	±0.2
USLS, beampeak to 20° above beampeak, dB	18	18	18	18	18	17	18
Front-to-Back Total Power at 180° ± 30°, dB	24	25	27	31	30	31	32
CPR at Boresight, dB	20	18	20	20	18	16	18
CPR at Sector, dB	11	9	9	11	12	11	11

Mechanical Specifications

Wind Loading @ Velocity, frontal	803.0 N @ 150 km/h (180.5 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	275.0 N @ 150 km/h (61.8 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	1,040.0 N @ 150 km/h (233.8 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	661.0 N @ 150 km/h (148.6 lbf @ 150 km/h)
Wind Speed, maximum	200 km/h (124 mph)

Packaging and Weights

Width, packed	565 mm 22.244 in
Depth, packed	312 mm 12.283 in
Length, packed	2286 mm 90 in
Weight, gross	60 kg 132.277 lb

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives

CCVVPX308.11R-C3

CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted




Included Products

T-029-GL-E	-	Adjustable Tilt Pipe Mounting Kit for 2.362"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.
------------	---	--

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---

T-029-GL-E



Adjustable Tilt Pipe Mounting Kit for 2.362"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

Product Classification

Product Type Adjustable tilt mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Length, maximum 2850 mm | 112.205 in

Compatible Length, minimum 1500 mm | 59.055 in

Compatible Diameter, maximum 115 mm | 4.528 in

Compatible Diameter, minimum 60 mm | 2.362 in

Antenna-to-Pipe Distance 85 mm | 3.346 in

Bracket-to-Bracket Distance 1400 mm | 55.118 in

Weight, net 6 kg | 13.228 lb

Material Specifications

Material Type Galvanized steel

Mechanical Specifications

Mechanical Tilt 0°-8°

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives

T-029-GL-E

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

