

4






3

2

1

- 1. GENERAL NOTES
 - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS
 - 1.2 FEATURES CRITICAL TO QUALITY ARE INDICATED IN ROUNDED BOX (X.X)
- 2. DESIGN NOTES
- 3. MANUFACTURING/SPECIAL REQUIREMENTS
 - 3.1 POWDER COAT PER COMMSCOPE'S PRODUCT COLOR/FINISH SPECIFICATION MTM1004 PER SUFFIX -XX.
- 4. TEST
- 5. PACKAGING
 - 5.1 PACK PER CS-PL-2044 REQUIREMENTS
- 6. SHOWN FOR REFERENCE ONLY

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	10937PC	PROTOTYPE RELEASE	TN1010	03/06/2021



COMMSCOPE, INC. OF NORTH CAROLINA										
TOLERANCES					SAP MATERIAL MASTER					
1 PLACE .X ± 0.2		3 PLACE .XXX ± 0.063			MTM1137-0000-XX					
2 PLACE .XX ± 0.13		ANGLES ± 1.0°								
FINISH SEE NOTES					MATERIAL AL5052-H32 SEE BOM					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	CE	TN1010	DATE	03/06/2021	ASSEMBLY, ENCLOSURE, DBHP					
	RW									
	RV									
	AD									
RE					SCALE	DOCUMENT NO.				
ECN	10937PC				1:8	SSC-760251532E1X				
SIZE	WORK AREA	INSL	MODEL			DRAWING				SHEET
C			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	1 OF 4	
			07	IW	A	00	IW	A		

DENSITY		lbs/in ³
MASS	205.42	lbs
VOLUME	4415.14	in ³
SURFACE AREA	28568.29	in ²
HEIGHT	56.0	
LENGTH	24.0	
WIDTH	17.5	