

FEATURES

- Non-latching 2x1 optical switch with 1263.5–1357.5 nm and 1423.5–1617.5 nm operating windows
- High sensitivity with wide range of user-settable switching thresholds: -32 to +21 dBm
- Fast switching time, 10 ms typical
- Low insertion loss, 1.0 dB typical
- Low power consumption
- Hot plug-in/out
- Local and remote status monitoring and control
- Occupies one half-depth slot

The CommScope OS32M1H-00-AS 2x1 optical switch module for the CH3000 platform offers high sensitivity, fast switching time, low insertion loss, and high packaging density.

Particularly well suited to protect long distance bi-directional links (using CWDM in the return path), this switch is designed to support traffic over alternate routing architectures and is guaranteed to have a switching time of less than 15 milliseconds. It will only switch to the secondary fiber route when the primary route optical input is below threshold setting and optical power on the alternate route is above threshold setting. Only light from A and B inputs is detected and used to control the switch (i.e., having high isolation from any input signals that may be present at the “Out” ports). Alternatively, the mode of operation may be set by the user to force operation using only the switch’s “A” or “B” position.



The switch has been designed with a wide dynamic threshold adjustment range to support any combination of both analog and digital transmission applications. The module is self-sensing of fiber restoration for maximum network reliability and efficiency and is fully controllable both locally and remotely.

The features of the OS32M1H-00 optical switch, including its single-width, half-depth design, makes it ideally suited to applications where high reliability is required and space and power consumption are important considerations.

SPECIFICATIONS

Characteristics	Specification
Physical	
Dimensions	6.6" D x 5.25" H x 1.0" W (3RU) (17 cm x 13.3 cm x 2.5 cm)
Weight	1.0 lb (0.45 kg)
Environmental	
Operating Temperature Range	-20° to +65°C (-4° to 149°F)
Storage Temperature Range	-40° to +85°C (-40° to +185°F)
Humidity	5% to 95% non-condensing
General	
Optical Connector	SC/APC
Switch Configuration	2x1
Switch Type	Non-latching
Switching Time	< 10 ms Typical, 15 ms Max
Switching Hysteresis	0.5 dB
	Hot plug-in/out
Optical	
Wavelength	1263.5 to 1357.5 nm and 1423.5 to 1617.5 nm NOTE: The threshold switching function only responds to wavelengths from 1530 to 1565 nm.
Insertion Loss	1.5 dB Max
Crosstalk	55 dB Min
Return Loss	55 dB Min
Polarization Dependent Loss	0.1 dB Max
Spectral Flatness	0.5 nm Max
Power Handling, Max (any Input Port)	22 dBm
Power Requirements	
Input Voltage	12 V _{DC} nominal from chassis resident power supply
Power Consumption	1.2 W
Local Controls and Monitoring	
Switching Threshold	Range: -32 to +21 dBm in 1 dB steps with ± 1.0 dB accuracy Hysteresis: 0.5 dB Typical
Operating Modes	Auto: switch operates based on threshold setting Force to A or B: switch latches in position A or B
Locally Monitored Parameters	Chassis slot number, powering voltage, internal temperature, input optical power, switch position ("A" or "B"), operating mode (Auto or Forced to A or B)
Front Panel Indicators	
Module Status LEDs	Red Alarm LED illuminated: input below threshold setting Blue Access LED illuminated: communication access
Switch Status LEDs	Green A LED illuminated: COM auto-switched to A position, or if blinking Forced to A Yellow B LED illuminated: COM auto-switched to B position, or if blinking Forced to B
Alarms	
	Service-affecting (DC failure, switch output below both input thresholds, switch forced to A or B position) and non-service-affecting (high internal temperature, A or B input power below threshold)

ORDERING INFORMATION

Model Name	Description
OS32M1H-00-AS	High Sensitivity 2x1 Optical Switch

RELATED PRODUCTS

CH3000 Chassis	Optical Patch Cords
Optical Transmitters	Optical Passives
BP Back Plates	Installation Services

Contact Customer Care for product information and sales:

- United States: 866-36-ARRIS
- International: +1-678-473-5656



Note: Specifications are subject to change without notice.

Copyright Statement: © 2023 CommScope, Inc. All rights reserved. ARRIS and the ARRIS logo are trademarks of CommScope, Inc. and/or its affiliates. All other trademarks are the property of their respective owners. No part of this content may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from CommScope, Inc and/or its affiliates ("CommScope"). CommScope reserves the right to revise or change this content from time to time without obligation on the part of CommScope to provide notification of such revision or change.

87-1069-RevD_OS32M1H-00_HighSensitivityOptSwitch