

# CT-15-CPUSE-DI6

15 dB, Tapper, 698–960/1710–2700 MHz



## OBSOLETE

This product was discontinued on: August 31, 2016

### Replaced By:

|                    |                                      |
|--------------------|--------------------------------------|
| CT-15-TCPUSE-43-I6 | 15 dB, Tapper, 340–960/1710-2700 MHz |
| CT-15-TCPUSE-DI6   | 15 dB, Tapper, 340–960/1710-2700 MHz |

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Product Type</b>          | Tapper  |

## General Specifications

|                              |                 |
|------------------------------|-----------------|
| <b>Device Type</b>           | Tapper          |
| <b>Application</b>           | Indoor/Outdoor  |
| <b>Color</b>                 | Silver          |
| <b>Inner Contact Plating</b> | Silver          |
| <b>Interface</b>             | 7-16 DIN Female |
| <b>Outer Contact Plating</b> | Trimetal        |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Height</b> | 28.9 mm   1.138 in  |
| <b>Width</b>  | 49.3 mm   1.941 in  |
| <b>Length</b> | 153.6 mm   6.047 in |

## Electrical Specifications

|                      |          |
|----------------------|----------|
| <b>3rd Order IMD</b> | -160 dBc |
|----------------------|----------|

# CT-15-CPUSE-DI6

---

|   |   |
|---|---|
| <b>3rd Order IMD Test Method</b>        | Two +43 dBm carriers                          |
| <b>Insertion Loss at Frequency Band</b> | 0.2 dB @ 1710–2700 MHz   0.2 dB @ 698–960 MHz |
| <b>Return Loss, minimum</b>             | 20.8 dB                                       |
| <b>Average Power, maximum</b>           | 300 W   |
| <b>Coupling</b>                         | 15 dB   |
| <b>Coupling Tolerance</b>               | ±1.25dB                                       |
| <b>Impedance</b>                        | 50 ohm  |
| <b>Operating Frequency Band</b>         | 1710 – 2700 MHz   698 – 960 MHz               |
| <b>Peak Power, maximum</b>              | 3 kW  |
| <b>Reflected Power, maximum</b>         | 200 W   |
| <b>VSWR</b>                             | 1.2   |

## Mechanical Specifications

|                                  |                        |
|----------------------------------|------------------------|
| <b>Coupling Nut Proof Torque</b> | 25 N-m   221.269 in lb |
|----------------------------------|------------------------|

## Environmental Specifications

|                                       |                                      |
|---------------------------------------|--------------------------------------|
| <b>Operating Temperature</b>          | -35 °C to +85 °C (-31 °F to +185 °F) |
| <b>Relative Humidity</b>              | Up to 100%                           |
| <b>Ingress Protection Test Method</b> | IEC 60529:2001, IP65                 |

## Packaging and Weights

|                       |   |
|-----------------------|---|
| <b>Height, packed</b> | 50 mm   1.969 in                                |
| <b>Width, packed</b>  | 95 mm   3.74 in                                 |
| <b>Length, packed</b> | 180 mm   7.087 in                               |
| <b>Volume</b>         | 855000 mm <sup>3</sup>   52.176 in <sup>3</sup> |
| <b>Weight, gross</b>  | 0.42 kg   0.926 lb                              |
| <b>Weight, net</b>    | 0.35 kg   0.772 lb                              |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

