

# PS-R-V4-M



PowerShift® V4 Main Shelf accommodates up to 3 boost modules (3 separate circuits per boost module for a total capacity of 9 RRUs) providing 24,372 watts of output power. Can be expanded to accommodate up to 6 boost modules powering 18 RRUs

- Reduced capital/operating expenditures
- Engineering flexibility
- Future-ready design

PowerShift® Macro V4 Main Shelf delivers the optimal voltage to your RRUs in real-time, automatically—regardless of power supply, distance, conductor size, or RRU power requirements. It optimizes backup power delivery by solving the voltage-drop problem. Inserted between the battery and trunk cable, PowerShift automatically senses and adjusts the battery's voltage output to the power cable to compensate for the voltage drop. As the battery discharges, PowerShift continues to boost output to maintain the optimal input voltage to the RRU to increase battery backup time. PowerShift® V4 Main Shelf accommodates up to 3 boost modules (PS-2000-73) per 1RU shelf. There are 3 separate circuits per boost module for a total capacity of 9 circuits (RRU's) per 1 RU shelf. Each circuit provides a maximum output of 2,708 Watts at 73Vdc and has an integrated bypass function that automatically passes the input power through to the load connections in case of a circuit failure. After the controller (PS-CNTRL-V4) calculates the voltage drop in the power cable due to line resistance, each circuit delivers about 2,000W at 54Vdc to the RRH input. The V4 Main Shelf can be expanded by adding an extension shelf (PS-R-V4-S) to power up to 18 circuits (RRU's) in 2 Rus.

- Reduced capital/operating expenditures
- Dynamic voltage regulation to the RRUs
- Service continuity with improved battery backup run time
- Significantly reduce installation time & wiring errors
- Future-ready design for higher-powered radios

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Shelf
<b>Product Brand</b>	PowerShift®
<b>Product Series</b>	V4
<b>Warranty</b>	For more information, please consult our Product Warranty guidelines

## General Specifications

<b>Application</b>	Mounts PowerShift® modules
<b>Backplane Interfaces</b>	10/100 Base-T Ethernet   One Galaxy Protocol (GP) RS485 bus
<b>Color</b>	Silver metallic
<b>Rack Type</b>	EIA 19 in

# PS-R-V4-M

---

<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	609.6 mm   24 in

## Electrical Specifications

<b>Input Voltage Range</b>	-38 to -58 Vdc
<b>Input Voltage, nominal</b>	-54 Vdc
<b>Output Power Connections, quantity</b>	9
<b>Output Voltage Range</b>	-48 to -73 Vdc
<b>Output Voltage, nominal</b>	-54 Vdc
<b>Electrical Safety Standard</b>	CAN/UL62368-1   CE   UL60950-UL/cUL with CB report
<b>Power Efficiency</b>	97 %

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Standards Compliance</b>	EN 55022 (Emissions)   RoHS Compliant   Telcordia™ GR-1089 Lightning /Surge   UL/cUL 62368

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	5.761 kg   12.7 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



\* Footnotes

**Warranty**

For more information, please consult our Product Warranty guidelines