


VZWSMART-MSK14 | UNIVERSAL ADJUSTABLE CROSSOVER



UNIVERSAL ADJUSTABLE CROSSOVER

Universal Adjustable Crossover Plate, connects up to 2-7/8" OD x 3-1/2" OD Pipe

Product Classification

Product Type	Clamp plate
Ordering Note	CommScope® non-standard product

General Specifications

Mounting	Crossover plate
-----------------	-----------------

Dimensions

Height	139.7 mm 5.5 in
Width	139.7 mm 5.5 in
Length	266.7 mm 10.5 in
Mounting Diameter 2, maximum	88.9 mm 3.5 in
Mounting Diameter 2, minimum	60.96 mm 2.4 in
Mounting Diameter, maximum	88.9 mm 3.5 in
Mounting Diameter, minimum	60.96 mm 2.4 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Packaging and Weights

Included	Hardware Plates
Packaging quantity	1
Weight, net	5 kg 11.023 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

VZWSMART-MSK14 | UNIVERSAL ADJUSTABLE CROSSOVER

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

