

Fiber OSP cable, LightScope ZWP® Blown Micro Single Jacket, 48 fiber, All-Dielectric Stranded Loose Tube Arid-Core® Construction, Gel-filled, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	B-LN


## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	2
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Subunit, quantity</b>	4
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	48

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	1.25 mm   0.049 in
<b>Diameter Over Jacket</b>	4.6 mm   0.181 in

## Representative Image



## Material Specifications

**Jacket Material** High density polyethylene (HDPE)

## Mechanical Specifications

**Minimum Bend Radius, loaded** 150 mm | 5.906 in

**Minimum Bend Radius, unloaded** 90 mm | 3.543 in

**Tensile Load, long term, maximum** 400 N | 89.924 lbf

**Tensile Load, short term, maximum** 1000 N | 224.809 lbf

**Compression** 5 N/mm | 28.551 lb/in

**Compression Test Method** IEC 60794-1-21 E3

**Flex** 25 cycles

**Flex Test Method** IEC 60794-1 E6

**Impact** 1 N-m | 8.851 in lb

**Impact Test Method** IEC 60794-1-21 E4

**Strain** See long and short term tensile loads

**Strain Test Method** IEC 60794-1-21 E1

**Twist** 10 cycles

**Twist Test Method** IEC 60794-1-21 E7

## Optical Specifications

**Fiber Type** G.652.D and G.657.A1

## Environmental Specifications

<b>Installation temperature</b>	-15 °C to +40 °C (+5 °F to +104 °F)
<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Cable Qualification Standards</b>	IEC 60794-5-10
<b>Environmental Space</b>	Air-blown, microduct
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F4

## Environmental Test Specifications

<b>Drip</b>	70 °C   158 °F
<b>Drip Test Method</b>	IEC 60794-1-21 E14
<b>Heat Age</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Heat Age Test Method</b>	IEC 60794-1-22 F9
<b>Temperature Cycle</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-22 F1

## Packaging and Weights

<b>Cable weight</b>	19 kg/km   12.767 lb/kft
---------------------	--------------------------

## Included Products

DB-8W-LT – LightScope ZWP® Singlemode  
Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable