

HFDC-24FIBER-P24S



HELIAX® Fiber Distribution Closure 24 fibers Single Mode

HELIAX® Fiber Distribution Closure 24 fibers Single Mode.2 HMFOC 12 fibers + additional 2 entries

Product Classification

Regional Availability	China EMEA Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®

General Specifications

Application	Used as a fiber junction box
Total Fiber Adapters	12
Color	Black
Doors, quantity	2
Mounting	Pipe, 44–114 mm (1.75–4.5 in) OD Wall
Total Fibers, quantity	24
Total Ports, quantity	12

Dimensions

Height	370 mm 14.567 in
Width	214 mm 8.425 in
Depth	118 mm 4.646 in
Jumper Breakout Length, Maximum	85 mm 3.346 in
Jumper Outlet, Quantity, Maximum	12
Jumper Outlet Diameter, Minimum	0 mm 0 in
Jumper Outlet Diameter, Maximum	7 mm 0.276 in

HFDC-24FIBER-P24S

Trunk Entry, Diameter, Minimum	5.5 mm 0.217 in
Trunk Entry, Diameter, Maximum	17.5 mm 0.689 in
Trunk Entry, Quantity, Maximum	4

Material Specifications

Material Type	High-impact polycarbonate, UV resistant
----------------------	---

Mechanical Specifications

Impact Test Method	EN62262 IEC62262: IK07
---------------------------	--------------------------

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Qualification Standards	IEC 60529, IP68

Packaging and Weights

Included	Mounting kit
Weight, net	2.88 kg 6.349 lb