5320303 | P3® 500 JCASST G SM MT



75 Ohm P3® Trunk and Distribution Cable, black PE jacket with coextruded green stripe, flooded for underground

*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability North America

Product Type Coaxial hardline cable

Product Brand P3®

Government RequirementsBuild America Buy America (BABA) compliant*

Warranty One year

General Specifications

Cable Type500 SeriesConstruction TypeSwaged

Jacket ColorBlack with co-extruded green stripe

Location of ManufacturingCatawba, North Carolina

Short Description P3 500 JCASST G SM MT PR7747

Dimensions

Cable Length731.52 m | 2400 ftDiameter Over Center Conductor, nominal2.769 mm | 0.109 in

Diameter Over Dielectric, nominal 11.481 mm | 0.452 in

Diameter Over Jacket, nominal 14.478 mm | 0.57 in

Diameter Over Outer Conductor, nominal 12.7 mm | 0.5 in

Jacket Thickness, nominal0.762 mm | 0.03 in

Outer Conductor Thickness, nominal 0.61 mm | 0.024 in

Electrical Specifications

Capacitance 50.197 pF/m | 15.3 pF/ft

COMMSCOPE®

5320303 | P3® 500 JCASST G SM MT

dc Resistance Note

Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal4.429 ohms/km | 1.35 ohms/kftdc Resistance, Loop, nominal5.643 ohms/km | 1.72 ohms/kftdc Resistance, Outer Conductor, nominal1.214 ohms/km | 0.37 ohms/kft

Jacket Spark Test Voltage5000 VacNominal Velocity of Propagation (NVP)87 %

Operating Frequency Band 5-3000 MHz

Structural Return Loss 24 dB @ 1003-1218 MHz | 24 dB @ 1219-1794 MHz | 30 dB @ 5-1002

MHz

Structural Return Loss, Grade N ≥24 dB @ 1003−1218 MHz | ≥24 dB @ 1219−1794 MHz | ≥30 dB @ 5−1002

MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.52	0.16
55.0	1.77	0.54
85.0	2.23	0.68
204.0	3.51	1.07
211.0	3.58	1.09
250.0	3.94	1.2
300.0	4.3	1.31
350.0	4.69	1.43
400.0	5.02	1.53
450.0	5.35	1.63
500.0	5.67	1.73
550.0	5.97	1.82
600.0	6.3	1.92
750.0	7.09	2.16
865.0	7.68	2.34
1002.0	8.32	2.54
1218.0	9.28	2.83
1500.0	10.68	3.26



Page 2 of 3

5320303 | P3® 500 JCASST G SM MT

1794.0	11.88	3.62
1800.0	11.91	3.63
2000.0	12.68	3.87
2200.0	13.44	4.1
2500.0	14.52	4.43
2700.0	15.22	4.64
3000.0	16.25	4.95

Material Specifications

Center Conductor Material Copper-clad aluminum

Dielectric Material Foam PE

Jacket Material PE

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded88.9 mm | 3.5 inPulling Tension, maximum136.078 kg | 300 lb

Environmental Specifications

Corrosion Protection Migraheal®

Packaging and Weights

Environmental Space

Packaging Type Reel

Weight, gross 183.044 kg/km | 123 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Buried

