## 530102203 | P3® 750 JCASS SM MT

75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground



#### Product Classification

Product Type	Coaxial hardline cable
Product Brand	P3®
Warranty	One year
General Specifications	
Cable Type	750 Series
Construction Type	Swaged
Jacket Color	Black
Dimensions	
Cable Length	762 m   2500 ft
Diameter Over Center Conductor, nominal	4.242 mm   0.167 in
Diameter Over Dielectric, nominal	17.323 mm   0.682 in
Diameter Over Jacket, nominal	21.082 mm   0.83 in
Diameter Over Outer Conductor, nominal	19.05 mm   0.75 in
Jacket Thickness, nominal	0.889 mm   0.035 in
Outer Conductor Thickness, nominal	0.864 mm   0.034 in
Electrical Specifications	
Capacitance	50.197 pF/m   15.3 pF/ft

Capacitance	50.197 pi/iii   15.5 pi/it
Capacitance Tolerance	±1.0 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 9, 2024



## 530102203 | P3® 750 JCASS SM MT

dc Resistance, Inner Conductor, nominal	1.87 ohms/km   0.57 ohms/kft
dc Resistance, Loop, nominal	2.493 ohms/km   0.76 ohms/kft
dc Resistance, Outer Conductor, nominal	0.623 ohms/km   0.19 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	87 %
Operating Frequency Band	5-3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz   24 dB @ 1219–1794 MHz   30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003−1218 MHz   ≥24 dB @ 1219−1794 MHz   ≥30 dB @ 5−1002 MHz

#### Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.36	0.11
55.0	1.21	0.37
85.0	1.51	0.46
204.0	2.36	0.72
211.0	2.43	0.74
250.0	2.66	0.81
300.0	2.92	0.89
350.0	3.18	0.97
400.0	3.44	1.05
450.0	3.67	1.12
500.0	3.87	1.18
550.0	4.07	1.24
600.0	4.3	1.31
750.0	4.86	1.48
865.0	5.28	1.61
1002.0	5.72	1.74
1218.0	6.41	1.95
1500.0	7.3	2.23
1794.0	8.07	2.46
1800.0	8.08	2.46
2000.0	8.57	2.61
2200.0	9.05	2.76

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 9, 2024



# 530102203 | P3® 750 JCASS SM MT

2500.0	9.73		2.96	
2700.0	10.16		3.1	
3000.0	10.8		3.29	
Material Specif	ications			
Center Conductor Mate	erial	Copper-clad aluminum		
Dielectric Material		Foam PE		
Jacket Material		PE		
Outer Conductor Mater	rial	Aluminum		
Mechanical Spe	ecifications			
Minimum Bend Radius,	, bonded	152.4 mm   6 in		
Pulling Tension, maxim	num	306.175 kg   675 lb		
Environmental	Specifications			
<b>Corrosion Protection</b>		Migraheal®		
Environmental Space		Buried		
Packaging and	Weights			
Packaging Type		Reel		
Weight, gross		398.828 kg/km   268 lb/kft		
Regulatory Compliance/Certifications				
Agency	Classification			

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 9, 2024

