5308303 | P3® 625 JCASP



75 Ohm P3® Trunk and Distribution Cable, black PE jacket with aerial floodant

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability North America

Product Type Coaxial hardline cable

Product Brand P3®

Government RequirementsBuild America Buy America (BABA) compliant*

Warranty One year

General Specifications

Cable Type625 SeriesConstruction TypeSwagedJacket ColorBlack

Location of ManufacturingCatawba, North CarolinaShort DescriptionP3 625 JCASP SM PR997

Dimensions

Cable Length731.52 m | 2400 ftDiameter Over Center Conductor, nominal3.48 mm | 0.137 inDiameter Over Dielectric, nominal14.351 mm | 0.565 inDiameter Over Jacket, nominal17.653 mm | 0.695 inDiameter Over Outer Conductor, nominal15.875 mm | 0.625 inJacket Thickness, nominal0.762 mm | 0.03 inOuter Conductor Thickness, nominal0.762 mm | 0.03 in

Electrical Specifications

Capacitance 50.197 pF/m | 15.3 pF/ft

COMMSCOPE®

5308303 | P3® 625 JCASP

dc Resistance Note Nominal values based on a standard condition of 20 °C (68 °F)

dc Resistance, Inner Conductor, nominal2.756 ohms/km | 0.84 ohms/kftdc Resistance, Loop, nominal3.609 ohms/km | 1.1 ohms/kftdc Resistance, Outer Conductor, nominal0.853 ohms/km | 0.26 ohms/kft

Jacket Spark Test Voltage5000 VacNominal Velocity of Propagation (NVP)87 %

Operating Frequency Band 5-3000 MHz

Structural Return Loss 24 dB @ 1003-1218 MHz | 24 dB @ 1219-1794 MHz | 30 dB @ 5-1002

MHz

Structural Return Loss, Grade N ≥24 dB @ 1003−1218 MHz | ≥24 dB @ 1219−1794 MHz | ≥30 dB @ 5−1002

MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.43	0.13
55.0	1.48	0.45
85.0	1.84	0.56
204.0	2.92	0.89
211.0	3.02	0.92
250.0	3.28	1
300.0	3.54	1.08
350.0	3.87	1.18
400.0	4.17	1.27
450.0	4.43	1.35
500.0	4.69	1.43
550.0	4.92	1.5
600.0	5.18	1.58
750.0	5.84	1.78
865.0	6.33	1.93
1002.0	6.92	2.11
1218.0	7.62	2.32
1500.0	8.74	2.66



5308303 | P3® 625 JCASP

1794.0	9.7	2.96
1800.0	9.72	2.96
2000.0	10.34	3.15
2200.0	10.95	3.34
2500.0	11.81	3.6
2700.0	12.37	3.77
3000.0	13.19	4.02

Material Specifications

Center Conductor Material Copper-clad aluminum

Dielectric Material Foam PE

Jacket Material PE

Outer Conductor Material Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded114.3 mm4.5 inPulling Tension, maximum215.456 kg475 lb

Environmental Specifications

Corrosion Protection Aerial floodant

Environmental Space Aerial

Packaging and Weights

Packaging Type Reel

Weight, gross 278.287 kg/km | 187 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

